

## QS 2/6.5/2.3 SAK4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Cross-connector (terminal), Plugged, beige, 44 A, Number of poles: 2, Pitch in mm (P): 6.50, Insulated: Yes, Width: 8.5 mm
Order No.	<a href="#">0212700000</a>
Type	QS 2/6.5/2.3 SAK4
GTIN (EAN)	4008190047269
Qty.	20 items

## QS 2/6.5/2.3 SAK4

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	37.5 mm	Depth (inches)	1.4764 inch
Height	12.5 mm	Height (inches)	0.4921 inch
Width	8.5 mm	Width (inches)	0.3346 inch
Net weight	5.45 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	20993c56-321a-4ec1-8646-b7d545a927f2

## Material data

Basic material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No		

## Dimensions

Pitch in mm (P)	6.50 mm	TS 35 offset	32 mm
-----------------	---------	--------------	-------

## General

Number of poles	2	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Rated voltage	400 V	Nominal current	44 A
---------------	-------	-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		