

TS 15X5/LL 2M/AL/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Aluminum has the second best electrical conductivity after copper. One advantage is low weight, another is outstanding corrosion protection.

General ordering data

Version	Terminal rail, Accessories, Aluminium, untreated, Width: 2000 mm, Height: 15 mm, Depth: 5.5 mm
Order No.	0217900000
Type	TS 15X5/LL 2M/AL/BK
GTIN (EAN)	4008190119034
Qty.	2 M
Delivery status	Discontinued
Available until	2022-03-31T00:00:00+02:00
Alternative product	TS 15X5/LL 2M/ST/ZN

TS 15X5/LL 2M/AL/BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.2165 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	50.5 g		

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%


Mounting rail

Solder eyelet hole diameter (D)	4.2 mm		
Installation advice	Direct mounting		
Standards	DIN EN 60715		
Surface finish	untreated		
Thickness	1.00 mm		
Basic material	Aluminium		
Length of the terminal rail	min.	0 mm	
	nominal	2000 mm	
	max.	2000 mm	
Permitted thermal current for PEN function, max.	76.00 A		
Slotted drill holes	Yes		
Slit length	12.00 mm		
Slit gap	8.00 mm		
Short-time withstand current per second according to IEC 60947-7-2	1.92 kA		
Slit width	4.20 mm		
Pre-punched mounting rail	Yes		
Slit width			
Short circuit strength corresponds to E-Cu wire	16.00 mm ²		
Drill-hole diameter	4.20 mm		
Spacing of holes, centre-to-centre	20 mm		
Slit gap			
Slit length			

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Drawings



TS 15X5/LL 2M/AL/BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

End bracket




Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EW 15	Version	
Order No.	0382860000	End bracket, beige, TS 15, V-2, Polyamide 66, Width: 10 mm, 100 °C	
GTIN (EAN)	4008190187804		
Qty.	50 ST		

Accessories




The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Type	SO SH1	Version	
Order No.	0401460000	Busbar support, grey, 100 °C, Width: 24.5 mm, V-2, Polyamide 66, when screwed in	
GTIN (EAN)	4008190188092		
Qty.	20 ST		

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EW 15/2	Version	
Order No.	1071900000	End bracket, dark beige, TS 15, HB, Plastic, Width: 8 mm, 100 °C	
GTIN (EAN)	4008190462949		
Qty.	50 ST		

TS 15X5/LL 2M/AL/BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	ZEW 15	Version	
Order No.	7920340000		End bracket, beige, TS 15, V-2, Plastic, Width: 5 mm, 120 °C
GTIN (EAN)	4032248238910		
Qty.	20 ST		