

**TS 35X15 2M/ST/ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

**General ordering data**

Version	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, Width: 2000 mm, Height: 35 mm, Depth: 15 mm
Order No.	<a href="#">0236400000</a>
Type	TS 35X15 2M/ST/ZN
GTIN (EAN)	4008190114558
Qty.	20 M

## TS 35X15 2M/ST/ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	570.37 g		

### Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Mounting rail

Installation advice	Direct mounting		
Standards	In accordance with DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		
Thickness	1.50 mm		
Basic material	Steel		
Length of the terminal rail	min.	0 mm	
	nominal	2000 mm	
	max.	2000 mm	
Short-time withstand current per second according to IEC 60947-7-2	4.2 kA		
Pre-punched mounting rail	No		
Slit width			
Short circuit strength corresponds to E-Cu wire	35.00 mm <sup>2</sup>		
Spacing of holes, centre-to-centre	0 mm		
Slit gap			
Slit length			

### Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

