

**MKL 3/12 WA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|                     |                                                                                                                                      |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Version             | Single- and multi-pole terminal strip, Solder connection, medium yellow, 2.5 mm <sup>2</sup> , 20 A, 400 V, Number of connections: 1 |
| Order No.           | <a href="#">0243620000</a>                                                                                                           |
| Type                | MKL 3/12 WA                                                                                                                          |
| GTIN (EAN)          | 4008190018320                                                                                                                        |
| Qty.                | 20 items                                                                                                                             |
| Delivery status     | Discontinued                                                                                                                         |
| Available until     | 2023-12-30T00:00:00+01:00                                                                                                            |
| Alternative product | <a href="#">MK 3/12</a>                                                                                                              |

## Technical data

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

|                       |                            |
|-----------------------|----------------------------|
| UL File Number Search | <a href="#">UL Website</a> |
|-----------------------|----------------------------|

|                      |        |
|----------------------|--------|
| Certificate No. (UR) | E60693 |
|----------------------|--------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 16.1 mm | Depth (inches)  | 0.6339 inch |
| Height     | 2300 mm | Height (inches) | 90.551 inch |
| Width      | 110 mm  | Width (inches)  | 4.3307 inch |
| Net weight | 34.65 g |                 |             |

### Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

### Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

### Material data

|                           |          |        |               |
|---------------------------|----------|--------|---------------|
| Basic material            | KrG      | Colour | medium yellow |
| UL 94 flammability rating | 5VA, V-0 |        |               |

### System specifications

|         |                        |                          |    |
|---------|------------------------|--------------------------|----|
| Version | For the mounting rails | End cover plate required | No |
|---------|------------------------|--------------------------|----|

### Additional technical data

|                     |                 |                          |    |
|---------------------|-----------------|--------------------------|----|
| Installation advice | Direct mounting | Explosion-tested version | No |
| Type of mounting    | Direct mounting |                          |    |

### CSA rating data

|                               |        |                       |           |
|-------------------------------|--------|-----------------------|-----------|
| Wire cross section max. (CSA) | 12 AWG | Voltage size C (CSA)  | 300 V     |
| Current size C (CSA)          | 25 A   | Certificate No. (CSA) | 12400-149 |
| Wire cross section min. (CSA) | 22 AWG |                       |           |

### Conductors for clamping (rated connection)

|                         |                   |                                         |                     |
|-------------------------|-------------------|-----------------------------------------|---------------------|
| Gauge to IEC 60947-1    | A2                | Wire connection cross section AWG, max. | AWG 12              |
| Connection direction    | on side           | Tightening torque, max.                 | 0.45 Nm             |
| Tightening torque, min. | 0.4 Nm            | Stripping length                        | 5 mm                |
| Type of connection      | Solder connection | Number of connections                   | 1                   |
| Clamping range, max.    | 4 mm <sup>2</sup> | Clamping range, min.                    | 0.5 mm <sup>2</sup> |
| Clamping screw          | M 2.5             | Blade size                              | 0.6 x 3.5 mm        |

## MKL 3/12 WA

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                                                                                         |                     |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------|---------------------|
| Wire connection cross section AWG, min.                                                 | AWG 22              | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> | Wire connection cross section, finely stranded, max.                                    | 1 mm <sup>2</sup>   |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> | Connection cross-section, stranded, max.                                                | 2.5 mm <sup>2</sup> |
| Connection cross-section, stranded, min.                                                | 1.5 mm <sup>2</sup> | Torque level with DMS electric screwdriver                                              | 1                   |
| Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>   | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup> |

## General

|                     |                 |                                         |        |
|---------------------|-----------------|-----------------------------------------|--------|
| Number of poles     | 12              | Wire connection cross section AWG, max. | AWG 12 |
| Installation advice | Direct mounting | Wire connection cross section AWG, min. | AWG 22 |

## Rating data

|                                              |                     |                                 |       |
|----------------------------------------------|---------------------|---------------------------------|-------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 400 V |
| Rated DC voltage                             | 400 V               | Nominal current                 | 20 A  |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 6 kV  |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Pollution severity              | 3     |

## UL rating data

|                                         |        |                                         |        |
|-----------------------------------------|--------|-----------------------------------------|--------|
| Conductor size Factory wiring max. (UR) | 12 AWG | Current size C (UR)                     | 20 A   |
| Voltage size C (UR)                     | 300 V  | Conductor size Factory wiring min. (UR) | 22 AWG |
| Certificate No. (UR)                    | E60693 | Conductor size Field wiring min. (UR)   | 22 AWG |
| Conductor size Field wiring max. (UR)   | 12 AWG |                                         |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001284    | ETIM 9.0    | EC001284    |
| ETIM 10.0   | EC001284    | ECLASS 14.0 | 27-14-11-06 |
| ECLASS 15.0 | 27-14-11-06 |             |             |