

D 2 MK5/2 PA/NA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Version	Terminal cover, white, PA 66, Height: 4000 mm, Width: 18 mm, Depth: 7.7 mm, V-2
Order No.	0244060000
Type	D 2 MK5/2 PA/NA
GTIN (EAN)	4008 19007 1844
Qty.	50 items

D 2 MK5/2 PA/NA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.7 mm	Depth (inches)	0.3031 inch
Height	4000 mm	Height (inches)	157.48 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	1.72 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66	Colour	white
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails	Mounting rail	Mounting plate
---------	------------------------	---------------	----------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

Conductors for clamping (rated connection)

Number of connections	4	Blade size	0.6 x 3.5 mm
-----------------------	---	------------	--------------

Dimensions

Fixing dimension	12 mm
------------------	-------

General

Installation advice	Direct mounting	Mounting rail	Mounting plate
---------------------	-----------------	---------------	----------------

Rating data

Pollution severity	3
--------------------	---

Technical data

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		