

CLI C 2-4 SW/WS 0 MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, black |
| Order No. | 0251311503 |
| Type | CLI C 2-4 SW/WS 0 MP |
| GTIN (EAN) | 4032248452569 |
| Qty. | 100 items |

CLI C 2-4 SW/WS 0 MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 8 mm | Depth (inches) | 0.315 inch |
| Height | 4 mm | Height (inches) | 0.1575 inch |
| Width | 7 mm | Width (inches) | 0.2756 inch |
| Net weight | 0.17 g | | |

Temperatures

Operating temperature range -30...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--|--|----------------|--|
| Material colour according to resistance code | 0 | | |
| Orientation of print | horizontal | | |
| Type of printing | Standard | | |
| Printing method | hot-embossing | | |
| Version | MultiPack | | |
| Width | 7 mm | | |
| UL 94 flammability rating | V-0 | | |
| Operating temperature range, max. | 80 °C | | |
| Operating temperature range, min. | -30 °C | | |
| Colour | black | | |
| Halogen | Yes | | |
| Insulation cross-section, max. | 10 | | |
| Basic material | PVC, soft, without Cadmium | | |
| Colour of printing | white | | |
| Printed characters | Numbers | | |
| Number of markers per packaging unit | Form of supply | Component part | |
| Recommended industries | Process, Machinery | | |
| Number of markers per combination | 1 Component part = Conductor and cable markers | | |
| Operating temperature range | -30...80 °C | | |
| Imprint | 0 | | |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Halogen | Yes | Conductor cross-section, max. | 16 mm ² |
| Conductor cross-section, min. | 2.5 mm ² | Conductor O.D., max. | 10 mm |
| Conductor O.D., min. | 4 mm | Conductor O.D. | 4 - 10 mm |
| Cross-section for connected wire | 2.5 - 16 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |