

## CLI C 2-4 GE/SW F MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |   |
|------------|---|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow |
| Order No.  | <a href="#">0251311647</a>  |
| Type       | CLI C 2-4 GE/SW F MP  |
| GTIN (EAN) | 4008190002008   |
| Qty.       | 100 items   |

## CLI C 2-4 GE/SW F MP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch  |
| Height     | 4 mm   | Height (inches) | 0.1575 inch |
| Width      | 7 mm   | Width (inches)  | 0.2756 inch |
| Net weight | 0.16 g |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|  |  |                |
|--|--|----------------|
| Material colour according to resistance code | 4  |                |
| Orientation of print                         | horizontal                                     |                |
| Type of printing                             | Standard                                       |                |
| Printing method                              | hot-embossing                                  |                |
| Version                                      | MultiPack                                      |                |
| Width  | 7 mm   |                |
| UL 94 flammability rating                    | V-0  |                |
| Operating temperature range, max.            | 80 °C  |                |
| Operating temperature range, min.            | -30 °C   |                |
| Colour                                       | yellow   |                |
| Halogen                                      | Yes  |                |
| Insulation cross-section, max.               | 10   |                |
| Basic material                               | PVC, soft, without Cadmium                     |                |
| Colour of printing                           | black  |                |
| Printed characters                           | Upper-case letters                             |                |
| Number of markers per packaging unit         | Form of supply                                 | Component part |
| Recommended industries                       | Process, Machinery                             |                |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |
| Operating temperature range                  | -30...80 °C                                    |                |
| Imprint                                      | F  |                |

### Conductor and cable markers

|                                  |                          |                               |                    |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Halogen                          | Yes                      | Conductor cross-section, max. | 16 mm <sup>2</sup> |
| Conductor cross-section, min.    | 2.5 mm <sup>2</sup>      | Conductor O.D., max.          | 10 mm              |
| Conductor O.D., min.             | 4 mm                     | Conductor O.D.                | 4 - 10 mm          |
| Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |                               |                    |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |



Similar to illustration