

CLI C 2-4 GE/SW N MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow
Order No.	0251311663
Type	CLI C 2-4 GE/SW N MP
GTIN (EAN)	4008190058333
Qty.	100 items

CLI C 2-4 GE/SW N MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	0.13 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	
Orientation of print	horizontal	
Type of printing	Standard	
Printing method	hot-embossing	
Version	MultiPack	
Width	7 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Colour	yellow	
Halogen	Yes	
Insulation cross-section, max.	10	
Basic material	PVC, soft, without Cadmium	
Colour of printing	black	
Printed characters	Upper-case letters	
Number of markers per packaging unit	Form of supply	Component part
Recommended industries	Process, Machinery	
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	-30...80 °C	
Imprint	N	

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	2.5 mm ²	Conductor O.D., max.	10 mm
Conductor O.D., min.	4 mm	Conductor O.D.	4 - 10 mm
Cross-section for connected wire	2.5 - 16 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



Similar to illustration