

## CLI C 2-4 WS/SW 4 MP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, white |
| Order No.  | <a href="#">0251310004</a>   |
| Type       | CLI C 2-4 WS/SW 4 MP   |
| GTIN (EAN) | 4032248007998  |
| Qty.       | 100 items  |

**CLI C 2-4 WS/SW 4 MP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch  |
| Height     | 4 mm   | Height (inches) | 0.1575 inch |
| Width      | 7 mm   | Width (inches)  | 0.2756 inch |
| Net weight | 0.13 g |                 |             |

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|  |  |                |  |
|--|--|----------------|--|
| Material colour according to resistance code | 9  |                |  |
| Orientation of print                         | horizontal                                     |                |  |
| Type of printing                             | Standard                                       |                |  |
| Printing method                              | hot-embossing                                  |                |  |
| Version                                      | MultiPack                                      |                |  |
| Width  | 7 mm   |                |  |
| UL 94 flammability rating                    | V-0  |                |  |
| Operating temperature range, max.            | 80 °C  |                |  |
| Operating temperature range, min.            | -30 °C   |                |  |
| Colour                                       | white  |                |  |
| Halogen                                      | Yes  |                |  |
| Insulation cross-section, max.               | 10   |                |  |
| Basic material                               | PVC, soft, without Cadmium                     |                |  |
| Colour of printing                           | black  |                |  |
| Printed characters                           | Numbers  |                |  |
| Number of markers per packaging unit         | Form of supply                                 | Component part |  |
| Recommended industries                       | Process, Machinery                             |                |  |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |  |
| Operating temperature range                  | -30...80 °C                                    |                |  |
| Imprint                                      | 4  |                |  |

**Conductor and cable markers**

|                                  |                          |                               |                    |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Halogen                          | Yes                      | Conductor cross-section, max. | 16 mm <sup>2</sup> |
| Conductor cross-section, min.    | 2.5 mm <sup>2</sup>      | Conductor O.D., max.          | 10 mm              |
| Conductor O.D., min.             | 4 mm                     | Conductor O.D.                | 4 - 10 mm          |
| Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |                               |                    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |



Similar to illustration