

CLI C 02-3 GE/SW 0 MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow |
| Order No. | 0252111502 |
| Type | CLI C 02-3 GE/SW 0 MP |
| GTIN (EAN) | 4008190054281 |
| Qty. | 200 items |

CLI C 02-3 GE/SW 0 MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 3.5 mm | Depth (inches) | 0.1378 inch |
| Height | 3 mm | Height (inches) | 0.1181 inch |
| Width | 3.4 mm | Width (inches) | 0.1339 inch |
| Net weight | 0.02 g | | |

Temperatures

Operating temperature range -30...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--|--|----------------|--|
| Material colour according to resistance code | 4 | | |
| Orientation of print | horizontal | | |
| Type of printing | Standard | | |
| Printing method | hot-embossing | | |
| Version | MultiPack | | |
| Width | 3.4 mm | | |
| UL 94 flammability rating | V-0 | | |
| Operating temperature range, max. | 80 °C | | |
| Operating temperature range, min. | -30 °C | | |
| Colour | yellow | | |
| Halogen | Yes | | |
| Basic material | PVC, soft, without Cadmium | | |
| Colour of printing | black | | |
| Printed characters | Numbers | | |
| Number of markers per packaging unit | Form of supply | Component part | |
| Recommended industries | Process, Machinery | | |
| Number of markers per combination | 1 Component part = Conductor and cable markers | | |
| Operating temperature range | -30...80 °C | | |
| Imprint | 0 | | |

Conductor and cable markers

| | | | |
|----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen | Yes | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.2 mm ² | Conductor O.D., max. | 3 mm |
| Conductor O.D., min. | 1.3 mm | Conductor O.D. | 1.3 - 3 mm |
| Cross-section for connected wire | 0.2 - 1.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings



Similar to illustration