

CLI C 1-9 SDR CD


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|---|
| Version | CableLine, Conductor and cable markers, 2.5 - 5 mm, 9 x 4.2 mm, To customer specification |
| Order No. | 0252809999 |
| Type | CLI C 1-9 SDR CD |
| GTIN (EAN) | 4008190021351 |
| Qty. | 125 items |

CLI C 1-9 SDR CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 5 mm | Depth (inches) | 0.1968 inch |
| Height | 9 mm | Height (inches) | 0.3543 inch |
| Width | 4.2 mm | Width (inches) | 0.1654 inch |
| Net weight | 0.15 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|----------------------------|-----------------------------------|---------------------------|
| Orientation of print | horizontal | Type of printing | To customer specification |
| Printing method | Ink jet technology | Version | CD |
| Width | 4.2 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 80 °C | Operating temperature range, min. | -30 °C |
| Colour | To customer specification | Halogen | Yes |
| Basic material | PVC, soft, without Cadmium | Colour of printing | black |
| Printed characters | To customer specification | Operating temperature range | -30...80 °C |
| Imprint | Custom printing | | |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | Yes | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Conductor O.D., max. | 5 mm |
| Conductor O.D., min. | 2.5 mm | Conductor O.D. | 2.5 - 5 mm |
| Cross-section for connected wire | 1.5 - 4 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings



Similar to illustration