

CLI C 3-9 GE/SW SL MP**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 8 - 16 mm, 9 x 11 mm, yellow
Order No.	0253511735
Type	CLI C 3-9 GE/SW SL MP
GTIN (EAN)	4008190027780
Qty.	20 items

CLI C 3-9 GE/SW SL MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	17 mm	Depth (inches)	0.6693 inch
Height	9 mm	Height (inches)	0.3543 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	1.05 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	
Orientation of print	horizontal	
Type of printing	Standard	
Printing method	hot-embossing	
Version	MultiPack	
Width	11 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Colour	yellow	
Halogen	Yes	
Insulation cross-section, max.	16	
Basic material	PVC, soft, without Cadmium	
Colour of printing	black	
Printed characters	Mixed characters	
Number of markers per packaging unit	Form of supply	Component part
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	-30...80 °C	
Imprint	SL	

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor O.D.	8 - 16 mm
Cross-section for connected wire	16 - 70 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings



Similar to illustration