

## Product image



Similar to illustration

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Version	Connecting sleeve (terminal), when screwed in, Width: 4.9 mm, Height: 4.9 mm, Depth: 8 mm, Number of poles: 1, Copper
Order No.	<a href="#">0266700000</a>
Type	VH 8/4.9/3.3
GTIN (EAN)	4008190152031
Qty.	100 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	8 mm	Depth (inches)	0.315 inch
Height	4.9 mm	Height (inches)	0.1929 inch
Width	4.9 mm	Width (inches)	0.1929 inch
Diameter	4.9 mm	Net weight	0.69 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Copper	Colour	grey
----------------	--------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

**Dimensions**

Diameter	4.9 mm
----------	--------

**General**

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		