


**TS 35X15/2.3 2M/CU/BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Copper has the best electrical conductivity of all metals used. The copper rail has the highest short-circuit protection.

**General ordering data**

Version	Terminal rail, Accessories, Copper, untreated, Width: 2000 mm, Height: 35 mm, Depth: 15 mm
Order No.	<a href="#">0270100000</a>
Type	TS 35X15/2.3 2M/CU/BK
GTIN (EAN)	4008190105136
Qty.	20 M

**TS 35X15/2.3 2M/CU/BK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	15 mm	Depth (inches)	0.5906 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	940 g		

**Temperatures**

Ambient temperature -5 °C...40 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Mounting rail**

Installation advice	Direct mounting	
Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	2.30 mm	
Basic material	Copper	
Length of the terminal rail	min.	0 mm
	nominal	2000 mm
	max.	2000 mm
Permitted thermal current for PEN function, max.	309.00 A	
Short-time withstand current per second according to IEC 60947-7-2	18 kA	
Pre-punched mounting rail	No	
Slit width		
Short circuit strength corresponds to E-Cu wire	150.00 mm <sup>2</sup>	
Spacing of holes, centre-to-centre	0 mm	
Slit gap		
Slit length		

**Classifications**

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

## Data sheet

**TS 35X15/2.3 2M/CU/BK**

## Drawings

