



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Connecting sleeve (terminal), when screwed in, Width: 4 mm, Height: 4 mm, Depth: 5 mm, Number of poles: 1, Copper
Order No.	<a href="#">0296800000</a>
Type	VH 4.9/4/2.8
GTIN (EAN)	4008 190008000
Qty.	100 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	4 mm	Width (inches)	0.1575 inch
Diameter	4 mm	Net weight	0.23 g

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Copper	Colour	grey
----------------	--------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

### Dimensions

Diameter	4 mm
----------	------

### General

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		