

**PS 4 F.STB 4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

|            |                                |
|------------|--------------------------------|
| Version    | Test adapter (terminal), 230 V |
| Order No.  | <a href="#">0299600000</a>     |
| Type       | PS 4 F.STB 4                   |
| GTIN (EAN) | 4008 190074043                 |
| Qty.       | 20 items                       |

## PS 4 F.STB 4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 42 mm  | Depth (inches)  | 1.6535 inch |
| Height     | 7.7 mm | Height (inches) | 0.3031 inch |
| Width      | 7.7 mm | Width (inches)  | 0.3031 inch |
| Net weight | 3.16 g |                 |             |

## Temperatures

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Ambient temperature              | -5 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C        |                                  |        |

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 8d191f1d-272c-40a1-8319-7de6fe5d9746 |

## Material data

|                           |              |        |     |
|---------------------------|--------------|--------|-----|
| Basic material            | Polyamide 66 | Colour | red |
| UL 94 flammability rating | V-2          |        |     |

## System specifications

Version Test plug

## Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| With snap-in pegs   | No              | Type of fixing   | Plugged |
| Installation advice | Direct mounting | Type of mounting | Plugged |

## Conductors for clamping (rated connection)

|   |                     |  |                    |
|---|---------------------|--|--------------------|
| Stripping length  | 5 mm                | Type of connection                                   | Plug-in connection |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm <sup>2</sup> | Wire connection cross section, finely stranded, max. | 4 mm <sup>2</sup>  |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> | Connection cross-section, stranded, max.             | 4 mm <sup>2</sup>  |

## Dimensions

Pitch in mm (P) 7.70 mm

## General

|                                   |        |                     |                 |
|-----------------------------------|--------|---------------------|-----------------|
| Number of poles                   | 1      | Installation advice | Direct mounting |
| Operating temperature range, max. | 100 °C |                     |                 |

## PS 4 F.STB 4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Rating data

|               |       |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002555    | ETIM 9.0    | EC002555    |
| ETIM 10.0   | EC002555    | ECLASS 14.0 | 27-25-03-04 |
| ECLASS 15.0 | 27-25-03-04 |             |             |