



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Connecting sleeve (terminal), when screwed in, Width: 5 mm, Height: 5 mm, Depth: 12.5 mm, Number of poles: 1, Copper
Order No.	<a href="#">0300800000</a>
Type	VH 12.5/5/3.4
GTIN (EAN)	4008190056179
Qty.	50 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	12.5 mm	Depth (inches)	0.4921 inch
Height	5 mm	Height (inches)	0.1968 inch
Width	5 mm	Width (inches)	0.1968 inch
Diameter	5.5 mm	Net weight	1.11 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	73c55621-8329-401d-bde2-7fd78e0e60e4

**Material data**

Basic material	Copper	Colour	grey
----------------	--------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Direct mounting
----------------	-----------------	---------------------	-----------------

**Dimensions**

Diameter	5.5 mm	TS 32 offset	32.5 mm
----------	--------	--------------	---------

**General**

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		