

**KISC M3X20.5/10 EK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Clamping yoke, Mounting screw, Steel
Order No.	<a href="#">0303000000</a>
Type	KISC M3X20.5/10 EK4
GTIN (EAN)	4008190163686
Qty.	100 items

## KISC M3X20.5/10 EK4

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	20 mm	Height (inches)	0.7874 inch
Width	4.8 mm	Width (inches)	0.189 inch
Diameter	3 mm	Net weight	1.16 g

## Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Steel	Surface finish	Miscellaneous
Colour	silver		

## System specifications

Version	for busbars
---------	-------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

## Dimensions

Diameter	3 mm	Metric size of the thread, external	3.00 mm
----------	------	-------------------------------------	---------

## General

Installation advice	Direct mounting	Surface finish	Miscellaneous
---------------------	-----------------	----------------	---------------

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		