



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 41 A, Number of poles: 10, Pitch in mm (P): 7.90, Insulated: No, Width: 77.1 mm
Order No.	<a href="#">0338300000</a>
Type	QL 10 SAK6N
GTIN (EAN)	4008190176679
Qty.	20 items

### Technical data

#### Approvals

ROHS	Conform
------	---------

#### Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	77.1 mm	Width (inches)	3.0354 inch
Net weight	3 g		

#### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

#### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

#### Material data

Basic material	Copper	Colour	grey
----------------	--------	--------	------

#### System specifications

Version	for cross-connection link
---------	---------------------------

#### Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

#### Dimensions

Pitch in mm (P)	7.90 mm
-----------------	---------

#### General

Number of poles	10	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

#### Rating data

Nominal current	41 A
-----------------	------

#### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		