


Q 4 SAK2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 24 A, Number of poles: 4, Pitch in mm (P): 6.00, Insulated: No, Width: 23.4 mm
Order No.	0337200000
Type	Q 4 SAK2.5
GTIN (EAN)	4008190142902
Qty.	50 items

Q 4 SAK2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	20.5 mm	Depth (inches)	0.8071 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	23.4 mm	Width (inches)	0.9213 inch
Net weight	6.98 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material CuSn Colour grey

System specifications

Version for cross-connection link

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
Explosion-tested version No

Dimensions

Pitch in mm (P) 6.00 mm

General

Number of poles 4 Installation advice Direct mounting

Rating data

Nominal current 24 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		