

**BFSC M5X45 PA/NA****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Mounting screw (Terminal), 5.00 mm, Polyamide 66, Depth: 8.5 mm, Width: 8.5 mm, Height: 45 mm
Order No.	<a href="#">0344400000</a>
Type	BFSC M5X45 PA/NA
GTIN (EAN)	4008190029203
Qty.	50 items

## BFSC M5X45 PA/NA

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	8.5 mm	Depth (inches)	0.3346 inch
Height	45 mm	Height (inches)	1.7716 inch
Width	8.5 mm	Width (inches)	0.3346 inch
Diameter	5 mm	Net weight	0.93 g

## Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Polyamide 66	Colour	Natural
UL 94 flammability rating	V-2		

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

## Dimensions

Diameter	5 mm	Metric size of the thread, external	5.00 mm
----------	------	-------------------------------------	---------

## General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		