

**STB 25 IH/RT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

|                     |   |
|---------------------|---|
| Version             | Socket (terminal), Plug-in depth: 13 mm, Depth: 30.5 mm |
| Order No.           | <a href="#">0343300000</a>                              |
| Type                | STB 25 IH/RT  |
| GTIN (EAN)          | 4008190034115   |
| Qty.                | 50 items  |
| Delivery status     | This article will no longer be available in the future. |
| Available until     | 2025-12-31T00:00:00+01:00                               |
| Alternative product | <a href="#">STB 21.6/IH/RT WTL6/3</a>                   |

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|          |         |                |             |
|----------|---------|----------------|-------------|
| Depth    | 30.5 mm | Depth (inches) | 1.2008 inch |
| Width    | 7.2 mm  | Width (inches) | 0.2835 inch |
| Diameter | 7.2 mm  | Net weight     | 4.28 g      |

**Temperatures**

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -50 °C...55 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 100 °C         |

**Environmental Product Compliance**

|                                      |                                      |  |  |
|--------------------------------------|--------------------------------------|--|--|
| RoHS Compliance Status               | Compliant with exemption             |  |  |
| RoHS Exemption (if applicable/known) | 6c                                   |  |  |
| REACH SVHC                           | Lead 7439-92-1                       |  |  |
| SCIP                                 | dce63e23-eea1-4eaa-9071-1c98fc8fa2ea |  |  |

**Material data**

|                           |       |        |     |
|---------------------------|-------|--------|-----|
| Basic material            | PA 66 | Colour | red |
| UL 94 flammability rating | V-2   |        |     |

**System specifications**

|         |                        |
|---------|------------------------|
| Version | For the mounting rails |
|---------|------------------------|

**Additional technical data**

|                  |                 |                          |    |
|------------------|-----------------|--------------------------|----|
| Type of fixing   | when screwed in | Explosion-tested version | No |
| Type of mounting | when screwed in |                          |    |

**Dimensions**

|          |        |               |       |
|----------|--------|---------------|-------|
| Diameter | 7.2 mm | Plug-in depth | 13 mm |
|----------|--------|---------------|-------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |