

## H4,0/9

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1  
• supplied loose in polybag

### General ordering data

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 9 mm, 9 mm, No |
| Order No.  | <a href="#">0373100000</a>                 |
| Type       | H4,0/9                                     |
| GTIN (EAN) | 4008190164669                              |
| Qty.       | 500 items                                  |
| Packaging  | loose                                      |

**H4,0/9**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E499744                    |

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 0.13 g |
|------------|--------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Technical data

| Description of article | Wire end ferrule without plastic collar | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

### Wire-end ferrules

|   |                   |                             |         |
|---|-------------------|-----------------------------|---------|
| Contact surface diameter (D1)           | 2.8 mm            | Contact surface length (L2) | 9 mm    |
| Collar diameter (D2)                    | 4 mm              | L1 in mm                    | 9.00 mm |
| Wire connection cross section AWG, max. | AWG 12            | Stripping length            | 9 mm    |
| Conductor cross-section                 | 4 mm <sup>2</sup> |                             |         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

**Drawings**

