

## Q 10 SAK2.5



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, grey, 24 A, Number of poles: 10, Pitch in mm (P): 6.00, Insulated: No, Width: 60.6 mm |
| Order No.  | <a href="#">0368700000</a>   |
| Type       | Q 10 SAK2.5  |
| GTIN (EAN) | 4008190107796  |
| Qty.       | 20 items   |

## Q 10 SAK2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 20.5 mm | Depth (inches)  | 0.8071 inch |
| Height     | 6 mm    | Height (inches) | 0.2362 inch |
| Width      | 60.6 mm | Width (inches)  | 2.3858 inch |
| Net weight | 17.5 g  |                 |             |

### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                |      |        |      |
|----------------|------|--------|------|
| Basic material | CuSn | Colour | grey |
|----------------|------|--------|------|

### System specifications

|         |                           |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

### Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing           | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No              |                     |                 |

### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 6.00 mm |
|-----------------|---------|

### General

|                 |    |                     |                 |
|-----------------|----|---------------------|-----------------|
| Number of poles | 10 | Installation advice | Direct mounting |
|-----------------|----|---------------------|-----------------|

### Rating data

|               |       |                 |      |
|---------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 24 A |
|---------------|-------|-----------------|------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |