

**Q 10 AKZ4SS****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Product image**

## Similar to illustration

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 10, Pitch in mm (P): 5.10, Insulated: No, Width: 59.9 mm
Order No.	<a href="#">0369300000</a>
Type	Q 10 AKZ4SS
GTIN (EAN)	4008190065744
Qty.	20 items
Delivery status	Discontinued
Available until	2023-12-31T00:00:00+01:00

## Q 10 AKZ4SS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	13 mm	Depth (inches)	0.5118 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	59.9 mm	Width (inches)	2.3583 inch
Net weight	10.6 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Cu Zn	Colour	grey
----------------	-------	--------	------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

## Dimensions

Pitch in mm (P)	5.10 mm
-----------------	---------

## General

Number of poles	10	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

## Rating data

Nominal current	32 A
-----------------	------

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		