

## H2,5/7

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

### General ordering data

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 7 mm, 7 mm, No |
| Order No.  | <a href="#">0373000000</a>                 |
| Type       | H2,5/7                                     |
| GTIN (EAN) | 4008190173463                              |
| Qty.       | 1000 items                                 |
| Packaging  | loose                                      |

**Technical data**

**Approvals**

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E499744                    |

**Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 0.07 g |
|------------|--------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Technical data**

| Description of article | Wire end ferrule without plastic collar | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

**Wire-end ferrules**

|   |                     |                             |         |
|---|---------------------|-----------------------------|---------|
| Contact surface diameter (D1)           | 2.2 mm              | Contact surface length (L2) | 7 mm    |
| Collar diameter (D2)                    | 3.4 mm              | L1 in mm                    | 7.00 mm |
| Wire connection cross section AWG, max. | AWG 14              | Stripping length            | 7 mm    |
| Conductor cross-section                 | 2.5 mm <sup>2</sup> |                             |         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

**Drawings**

