

**TS 35X7.5 1M/ST/ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

**General ordering data**

Version	Terminal rail, Accessories, Steel, galvanized, chromium-plated, Width: 1000 mm, Height: 35 mm, Depth: 7.5 mm
Order No.	<a href="#">0383410000</a>
Type	TS 35X7.5 1M/ST/ZN
GTIN (EAN)	4008190115623
Qty.	20 M

**TS 35X7.5 1M/ST/ZN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	1000 mm	Width (inches)	39.37 inch
Net weight	10 g		

**Temperatures**

Ambient temperature -5 °C...40 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Mounting rail**


Installation advice	Direct mounting		
Standards	DIN EN 60715		
Surface finish	galvanized, chromium-plated		
Thickness	1.00 mm		
Basic material	Steel		
Length of the terminal rail	min.	0 mm	
	nominal	1000 mm	
	max.	1000 mm	
Short-time withstand current per second according to IEC 60947-7-2	1.92 kA		
Pre-punched mounting rail	No		
Slit width			
Short circuit strength corresponds to E-Cu wire	16.00 mm <sup>2</sup>		
Spacing of holes, centre-to-centre	0 mm		
Slit gap			
Slit length			

**Classifications**

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

**Product image**

---



Similar to illustration

---

---