
Data sheet

QL 3 SAKG54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 415 A, Number of poles: 3, Pitch in mm (P): 54.00, Insulated: No, Width: 148 mm
Order No.	0408000000
Type	QL 3 SAKG54
GTIN (EAN)	4008190069711
Qty.	5 items
Delivery status	Discontinued
Available until	2024-08-15T00:00:00+02:00

Data sheet

QL 3 SAKG54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	17 mm	Height (inches)	0.6693 inch
Width	148 mm	Width (inches)	5.8268 inch
Net weight	281.6 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	CuSn	Colour	grey

System specifications

Version	Cross-connector

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	54.00 mm

General

Number of poles	3	Installation advice	Direct mounting

Rating data

Nominal current	415 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		