

DQS 2 1D PS2,3 AG**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The component plug is used to integrate an electrical component in a disconnect terminal block. After soldering the electronic component, the plug can be integrated into the disconnection area of our disconnect terminal blocks and thus changes the disconnect terminal block into a modular terminal block with integrated electronic component.

General ordering data

Version	Plug (terminal), 6 mm ² , 1 A, Number of connections: 1, Number of poles: 2, Width: 6 mm
Order No.	0471460000
Type	DQS 2 1D PS2,3 AG
GTIN (EAN)	4008 19003589 1
Qty.	20 items
Delivery status	Discontinued
Available until	2025-12-31T00:00:00+01:00

DQS 2 1D PS2,3 AG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	40.5 mm	Depth (inches)	1.5945 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	3.55 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a
REACH SVHC	Lead 7439-92-1
SCIP	84c6cd16-7387-47f8-b14d-916300fbf4d4

Material data

Basic material	Wemid	Colour	beige
UL 94 flammability rating	V-0		

System specifications

Version	Diode module
---------	--------------

Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	Plugged

Conductors for clamping (rated connection)

Number of connections	1
-----------------------	---

Dimensions

Pitch in mm (P)	12.00 mm	TS 35 offset	35 mm
-----------------	----------	--------------	-------

General

Number of poles	2	Installation advice	Direct mounting
Operating temperature range, max.	120 °C		

Rating data

Rated cross-section	6 mm ²	Nominal current	1 A
---------------------	-------------------	-----------------	-----

Technical data

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		