

**ZB 4K SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Product image**



Similar to illustration

Weidmueller offers tapping terminals for various types of bus bar systems. Depending on the application, a distinction can be made here between insulated and non-insulated tap-off terminals.

**General ordering data**

Version	Terminal (busbar connection)
Order No.	<a href="#">0475310000</a>
Type	ZB 4K SW
GTIN (EAN)	4008 190008406
Qty.	50 items

## ZB 4K SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E60693
Certificate No. (cURusEX)	E184763

## Dimensions and weights

Depth	20.4 mm	Depth (inches)	0.8031 inch
Height	19 mm	Height (inches)	0.748 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	3.72 g		

## Temperatures

Ambient temperature -5 °C...40 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Steel	Insulating material	PA
Colour	black		

## Rating data IECEx/ATEX

Ex 2014/34/EU label	II 2 G D	Safety notice	<p>Installation instructions: The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31.</p> <p>When combined with other terminal block ranges and sizes, and when other accessories are used, you must comply with the clearance and creepage distances given. Regarding accessory use, the manufacturer's</p>
---------------------	----------	---------------	--

## ZB 4K SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

instructions must be followed.  
 List of restrictions:  
 The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.

### System specifications

Version for busbar 10 x 3 mm

### Additional technical data

Installation advice Feed-through (bushing) Type of mounting when screwed in

### CSA rating data

Wire cross section max. (CSA)	10 AWG	Certificate No. (CSA)	12400-237
Wire cross section min. (CSA)	26 AWG		

### Conductors for clamping (rated connection)

Tightening torque, max.	1 Nm	Tightening torque, min.	0.5 Nm
Type of connection	Clamping yoke	Clamping range, max.	6 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping screw	M 3
Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>
Connection cross-section, stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	6 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

### Dimensions

TS 35 offset 41 mm

### General

Installation advice Feed-through (bushing)

### Rating data

Rated cross-section 4 mm<sup>2</sup>

### UL rating data

Conductor size Factory wiring max. (UR)	12 AWG	Conductor size Factory wiring min. (UR)	20 AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR)	20 AWG
Conductor size Field wiring max. (UR)	12 AWG		

## Technical data

### Classifications

ETIM 8.0	EC000001	ETIM 9.0	EC000001
ETIM 10.0	EC000001	ECLASS 14.0	27-25-01-16
ECLASS 15.0	27-25-01-16		