


EGD2 EG2 5..240VAC/1A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



EGD rectifier components can be mounted on terminal rails.
 The bridge circuit consists of four individual diodes with a wide input voltage range of 5...240 Vac.
 The industry-standard rectifier switches are protected from overvoltage on both the input and output sides with varistors.

General ordering data

Version	Rectifier circuit, Surge protection with varistor
Order No.	0546260000
Type	EGD2 EG2 5..240VAC/1A
GTIN (EAN)	4008190103705
Qty.	10 items

EGD2 EG2 5..240VAC/1A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	58 mm	Height (inches)	2.2835 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	36.87 g		

Temperatures

Storage temperature	-45 °C...100 °C	Operating temperature	-30 °C...40 °C
---------------------	-----------------	-----------------------	----------------

Probability of failure

MTTF 11414 a

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a
REACH SVHC	Lead 7439-92-1
SCIP	e1c85f97-efe9-452e-b160-3df02d7555ab

General data

Segment	Measurement - Monitoring - Setting	Version	Surge protection for measurement and control
Design	Component housing	Width + mounting tolerance	20.2 mm
Height with TS 35	63 mm	Height with TS 32	67.5 mm

Input

Rated control voltage	230 V AC	Rated current AC	2,5 A
-----------------------	----------	------------------	-------

General data

Design	Component housing	Version	Surge protection for measurement and control
--------	-------------------	---------	---

Insulation coordination

Surge voltage category	II	Pollution severity	2
------------------------	----	--------------------	---

Connection data

Cross-section	2.5 mm ²	Type of connection	Screw connection
Tightening torque, min.	0.4 Nm	Tightening torque, max.	0.6 Nm
Clamping range, rated connection	4 mm ²	Clamping range, min.	0.5 mm ²
Clamping range, max.	4 mm ²	Wire connection cross section AWG, max.	AWG 12

EGD2 EG2 5..240VAC/1A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Wire connection cross section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	4 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm ²

Classifications

ETIM 8.0	EC002540	ETIM 9.0	EC002540
ETIM 10.0	EC002540	ECLASS 14.0	27-04-03-90
ECLASS 15.0	27-04-03-90		

