

CLI R 1 F. CLI C 1-3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | |
|------------|-----------------------------|
| Version | CableLine, Mounting mandrel |
| Order No. | 0532100000 |
| Type | CLI R 1 F. CLI C 1-3 |
| GTIN (EAN) | 4008190092191 |
| Qty. | 20 items |

CLI R 1 F. CLI C 1-3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 2 mm | Depth (inches) | 0.0787 inch |
| Height | 150 mm | Height (inches) | 5.9055 inch |
| Width | 2.5 mm | Width (inches) | 0.0984 inch |
| Net weight | 1.05 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|--|-----------|-----------------------------------|--------------------|
| Material colour according to resistance code | 6 | Type of printing | Standard |
| Version | MultiPack | Width | 2.5 mm |
| UL 94 flammability rating | V-0 | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Colour | blue |
| Halogen | Yes | Basic material | POM |
| Printed characters | Numbers | Recommended industries | Process, Machinery |
| Number per mandrel | 25 | Operating temperature range | -30...80 °C |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | Yes | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Conductor O.D., max. | 5 mm |
| Conductor O.D., min. | 2.5 mm | Conductor O.D. | 2.5 - 5 mm |
| Cross-section for connected wire | 1.5 - 4 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |