


**CLI O 10-3 GE/SW O MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers. Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

|            |                                                                    |
|------------|--------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 2 - 3 mm, 3 x 4 mm, yellow |
| Order No.  | <a href="#">0648001665</a>                                         |
| Type       | CLI O 10-3 GE/SW O MP                                              |
| GTIN (EAN) | 4008190147723                                                      |
| Qty.       | 200 items                                                          |

## CLI O 10-3 GE/SW O MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 4 mm   | Depth (inches)  | 0.1575 inch |
| Height     | 3 mm   | Height (inches) | 0.1181 inch |
| Width      | 4 mm   | Width (inches)  | 0.1575 inch |
| Net weight | 0.02 g |                 |             |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                              |                    |                                   |                            |
|----------------------------------------------|--------------------|-----------------------------------|----------------------------|
| Material colour according to resistance code | 4                  | Orientation of print              | horizontal                 |
| Type of printing                             | Standard           | Printing method                   | hot-embossing              |
| Version                                      | MultiPack          | Width                             | 4 mm                       |
| UL 94 flammability rating                    | V-0                | Operating temperature range, max. | 80 °C                      |
| Operating temperature range, min.            | -30 °C             | Colour                            | yellow                     |
| Halogen                                      | Yes                | Basic material                    | PVC, soft, without Cadmium |
| Colour of printing                           | black              | Printed characters                | Upper-case letters         |
| Recommended industries                       | Process, Machinery | Operating temperature range       | -30...80 °C                |
| Imprint                                      | O                  |                                   |                            |

## Conductor and cable markers

|                                  |                           |                               |                     |
|----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen                          | Yes                       | Conductor cross-section, max. | 1.5 mm <sup>2</sup> |
| Conductor cross-section, min.    | 0.4 mm <sup>2</sup>       | Conductor O.D., max.          | 3 mm                |
| Conductor O.D., min.             | 2 mm                      | Conductor O.D.                | 2 - 3 mm            |
| Cross-section for connected wire | 0.4 - 1.5 mm <sup>2</sup> |                               |                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration