


**CLI O 20-3 GE/SW W MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers. Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

Version	CableLine, Conductor and cable markers, 3 - 4 mm, 3 x 5.5 mm, yellow
Order No.	<a href="#">0648101683</a>
Type	CLI O 20-3 GE/SW W MP
GTIN (EAN)	4008190038083
Qty.	200 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	5 mm	Depth (inches)	0.1968 inch
Height	3 mm	Height (inches)	0.1181 inch
Width	5.5 mm	Width (inches)	0.2165 inch
Net weight	0.04 g		

**Temperatures**

Operating temperature range	-30...80 °C
-----------------------------	-------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Material colour according to resistance code	4	Orientation of print	horizontal
Type of printing	Standard	Printing method	hot-embossing
Version	MultiPack	Width	5.5 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Colour	yellow
Halogen	Yes	Basic material	PVC, soft, without Cadmium
Colour of printing	black	Printed characters	Upper-case letters
Recommended industries	Process, Machinery	Operating temperature range	-30...80 °C
Imprint	W		

**Conductor and cable markers**

Halogen	Yes	Conductor cross-section, max.	3 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Conductor O.D., max.	4 mm
Conductor O.D., min.	3 mm	Conductor O.D.	3 - 4 mm
Cross-section for connected wire	1.5 - 3 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



Similar to illustration