

## CLI O 30-3 GE/SW C MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers. Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 4 - 5 mm, 3 x 6 mm, yellow |
| Order No.  | <a href="#">0648201641</a>   |
| Type       | CLI O 30-3 GE/SW C MP  |
| GTIN (EAN) | 4008 190186654   |
| Qty.       | 200 items  |

**CLI O 30-3 GE/SW C MP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 6 mm   | Depth (inches)  | 0.2362 inch |
| Height     | 3 mm   | Height (inches) | 0.1181 inch |
| Width      | 6 mm   | Width (inches)  | 0.2362 inch |
| Net weight | 0.04 g |                 |             |

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|  |                    |                                   |                            |
|--|--------------------|-----------------------------------|----------------------------|
| Material colour according to resistance code | 4                  | Orientation of print              | horizontal                 |
| Type of printing                             | Standard           | Printing method                   | hot-embossing              |
| Version                                      | MultiPack          | Width                             | 6 mm                       |
| UL 94 flammability rating                    | V-0                | Operating temperature range, max. | 80 °C                      |
| Operating temperature range, min.            | -30 °C             | Colour                            | yellow                     |
| Halogen                                      | Yes                | Basic material                    | PVC, soft, without Cadmium |
| Colour of printing                           | black              | Printed characters                | Upper-case letters         |
| Recommended industries                       | Process, Machinery | Operating temperature range       | -30...80 °C                |
| Imprint                                      | C                  |                                   |                            |

**Conductor and cable markers**

|                                  |                       |                               |                   |
|----------------------------------|-----------------------|-------------------------------|-------------------|
| Halogen                          | Yes                   | Conductor cross-section, max. | 4 mm <sup>2</sup> |
| Conductor cross-section, min.    | 3 mm <sup>2</sup>     | Conductor O.D., max.          | 5 mm              |
| Conductor O.D., min.             | 4 mm                  | Conductor O.D.                | 4 - 5 mm          |
| Cross-section for connected wire | 3 - 4 mm <sup>2</sup> |                               |                   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |



Similar to illustration