




Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**







To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

#### **General ordering data**

Version	Multi-tier modular terminal, Screw connection, beige / yellow, 4 mm², 500 V, Number of connec- tions: 4, Number of levels: 2, TS 32, V-2
Order No.	<u>0590260000</u>
Туре	DK 4QV/32
GTIN (EAN)	4008190022419
Qty.	25 items





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Technical data

|--|

Approvals







쏡

ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (UR)	E60693

## **Dimensions and weights**

Depth	59.5 mm	Depth (inches)	2.3425 inch
Height	54 mm	Height (inches)	2.126 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	14.46 a		

## **Temperatures**

Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### **Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

#### **Material data**

Basic material	PA 66	Colour	beige / yellow
UL 94 flammability rating	V-2		

#### **Rating data IECEx/ATEX**

Certificate No. (ATEX)	TUEV18ATEX8210U	Certificate No. (IECEX)	IECEXTUR18.0020U
Max. voltage (ATEX)	275 V	Current (ATEX)	28 A
Wire cross section max. (ATEX)	4 mm²	Max. voltage (IECEX)	275 V
Current (IECEX)	28 A	Wire cross section max. (IECEX)	4 mm²
Marking EN 60079-7	Ex eb II C Gb	Ex 2014/34/EU label	II 2 G D

## **System specifications**

Version	Screw connection, Vertically cross-connected, for screwable cross- connection, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	2
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	Yes	PE connection	No
Mounting rail	TS 32	N-function	No
PE function	No	PEN function	No

Creation date 04.11.2025 07:01:03 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Technical data

Additional technical data			
Additional teemineal data			
Open sides	right	Number of similar terminals	1
Explosion-tested version	Yes	Type of mounting	Clamped
CSA rating data	1		
Jori ruting data			
Wire cross section max. (CSA)	12 AWG	Voltage size C (CSA)	300 V
Current size C (CSA)	10 A	Certificate No. (CSA)	12400-124
Vire cross section min. (CSA)	26 AWG		
Conductors for clamping (add	litional connection)		
Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.	2.5 mm <sup>2</sup>	Connection type, additional connection	Screw connection
Conductors for clamping (rate	ed connection)		
Gauge to IEC 60947-1	A3	Wire connection cross section AWG, max.	AWG 12
Connection direction	on side	Tightening torque, max.	0.1 Nm
Γightening torque, min.	0.5 Nm	Stripping length	8 mm
ype of connection 2	Screw connection	Type of connection	Screw connection
lumber of connections	4	Clamping range, max.	6 mm <sup>2</sup>
Clamping range, min.	0.13 mm <sup>2</sup>	Clamping screw	M 3
Blade size	0.6 x 3.5 mm	Wire connection cross section AWG, min.	AWG 26
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	2.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.13 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	2.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.13 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	4 mm²	Wire connection cross section, finely stranded, min.	0.13 mm <sup>2</sup>
Connection cross-section, stranded, max.	4 mm <sup>2</sup>	Connection cross-section, stranded, min	.0.13 mm <sup>2</sup>
Twin wire-end ferrules, max.	1.5 mm <sup>2</sup>	Twin wire-end ferrules, min.	0.5 mm <sup>2</sup>
Torque level with DMS electric screwdriver	2	Wire connection cross-section, solid core, max.	6 mm²
Wire connection cross-section, solid core, min.	0.13 mm <sup>2</sup>	Connection cross-section, finely stranded, min.	0.13 mm <sup>2</sup>
General			
Wire connection cross section AWG,	AWG 12	Wire connection cross section AWG, min.	AWG 26
Standards	IEC 60947-7-1	Mounting rail	TS 32
Rating data			
Rated cross-section	4 mm <sup>2</sup>	Rated voltage	500 V
Rated DC voltage	500 V	Nominal current	32 A
Current at maximum wires	41 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC	1.02 W	Pollution severity	3

Creation date 04.11.2025 07:01:03 MEZ





### Weidmüller Interface GmbH & Co. KG

4

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

## **UL** rating data

Conductor size Factory wiring ma	ax. (UR) 12 AWG	Current size C (UR) 27	A
Voltage size C (UR)	300 V	Conductor size Factory wiring min. (UR) 26	AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR) 22	AWG
Conductor size Field wiring max.	(UR) 12 AWG		

#### Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 9.0	27-14-11-20
ECLASS 9.1	27-14-11-20	ECLASS 10.0	27-14-11-20
ECLASS 11.0	27-14-11-20	ECLASS 12.0	27-14-11-20
ECLASS 13.0	27-25-01-02	ECLASS 14.0	27-25-01-02
ECLASS 15.0	27-25-01-02		



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Cross-connections**









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

#### **General ordering data**

Туре	Q 2 AKZ4	Version
Order No.	0336400000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN (EAN)	4008190037680	poles: 2, Pitch in mm (P): 6.10, Insulated: No, Width: 11.1 mm
Qty.	50 ST	
Туре	Q 3 AKZ4	Version
Type Order No.	Q 3 AKZ4 0336500000	Version Cross-connector (terminal), when screwed in, grey, 24 A, Number of

#### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

#### General ordering data

	- · · · <b>J</b> · · · ·	
Туре	Q 4 AKZ4	Version
Order No.	0336600000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN (EAN)	4008190096656	poles: 4, Pitch in mm (P): 6.10, Insulated: No, Width: 23.3 mm
Qty.	50 ST	

#### **Cross-connections**









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **General ordering data**

Type	Q 2 AKZ	1.5	Version
Order	No. <u>036820</u>	0000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN	(EAN) 400819	0149987	poles: 2, Pitch in mm (P): 5.10, Insulated: No, Width: 9.1 mm
Qty.	50 ST		

#### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

#### **General ordering data**

Туре	Q 3 AKZ1.5	Version
Order No.	0368300000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN (EAN)	4008190074913	poles: 3, Pitch in mm (P): 5.10, Insulated: No, Width: 14.2 mm
Qty.	50 ST	

#### **Cross-connections**









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### **General ordering data**

Туре	Q 4 AKZ1.5	Version
Order No.	0368400000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN (EAN)	4008190153892	poles: 4, Pitch in mm (P): 5.10, Insulated: No, Width: 19.3 mm
Qty.	50 ST	
Туре	Q 10 AKZ1.5	Version
Order No.	0368500000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN (EAN)	4008190159481	poles: 10, Pitch in mm (P): 5.10, Insulated: No, Width: 49.9 mm
Qty.	20 ST	
Туре	Q 10 AKZ4	Version
Order No.	0368600000	Cross-connector (terminal), when screwed in, grey, 24 A, Number of
GTIN (EAN)	4008190056766	poles: 10, Pitch in mm (P): 6.10, Insulated: No, Width: 59.9 mm
Qty.	20 ST	
Qty.	2031	
Туре	Q 2 AKZ4SS	Version
,		Version Cross-connector (terminal), when screwed in, grey, 32 A, Number of
Туре	Q 2 AKZ4SS	

Creation date 04.11.2025 07:01:03 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

#### **General ordering data**

Type	Q 10 AKZ4SS	Version
Order No.	0369300000	Cross-connector (terminal), when screwed in, grey, 32 A, Number of
GTIN (EAN)	4008190065744	poles: 10, Pitch in mm (P): 5.10, Insulated: No, Width: 59.9 mm
Qty.	20 ST	
Туре	QB 2 WI RA6 IS	Version
Type Order No.	QB 2 WI RA6 IS 0482700000	Version Cross-connector (terminal), when screwed in, grey, 27 A, Number of
• •		

#### **Cross-connections**









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### **General ordering data**

Туре	QB 3 WI RA6 IS	Version
Order No.	0482800000	Cross-connector (terminal), when screwed in, grey, 27 A, Number of
GTIN (EAN)	4008190145217	poles: 3, Pitch in mm (P): 6.00, Insulated: Yes, Width: 3 mm
Qty.	50 ST	

#### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **General ordering data**

Туре	QB 4 WI RA6 IS	Version
Order No.	0482900000	Cross-connector (terminal), when screwed in, grey, 27 A, Number of
GTIN (EAN)	4008190086169	poles: 4, Pitch in mm (P): 6.00, Insulated: Yes, Width: 3 mm
Qty.	50 ST	

#### **End plates and partition plates**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

#### **General ordering data**

	onoral ordoning data		
Туре	AP DK4Q	Version	
Order No.	<u>1397160000</u>	End plate for terminals, beige, Height: 54 mm, Width: 1.5 mm, V-2,	
GTIN (EAN)	4008190125899	PA 66, Snap-on: Yes	
Qty.	20 ST		
Туре	AP DK4Q BL	Version	
Order No.	<u>1397180000</u>	End plate for terminals, blue, Height: 54 mm, Width: 1.5 mm, V-2, PA	
GTIN (EAN)	4008190171728	66, Snap-on: Yes	
Qty.	20 ST		
Туре	TW SAKS2 HP/DBR/2	Version	
Order No.	0607000000	Partition plate (terminal), dark brown, Height: 80 mm, Width: 2 mm,	
GTIN (EAN)	4008190002732	V-2, PA 66	
Qty.	20 ST		
Туре	WTW EN	Version	
Order No.	1058800000	Partition plate (terminal), dark beige, Height: 86 mm, Width: 3 mm,	
GTIN (EAN)	4008190140175	V-0, Wemid	
Qty.	20 ST		
Туре	TSCH 6 DKI S4	Version	
Order No.	0190260000	Small partition (terminal), PA 66, beige, Continuous operating temp.,	
GTIN (EAN)	4008190051075	max.: 100 °C	
Qty.	100 ST		

#### **Testadapter and testsockets**



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **General ordering data**

Type	PS 2.3 RT	Version
Order No.	0180400000	Test adapter (terminal), 230 V, 20 mA
GTIN (EAN)	4008190060121	
Qty.	20 ST	
Туре	STB 8.5/D4/2.3/M2.5 AKZ	Version
Type Order No.	STB 8.5/D4/2.3/M2.5 AKZ 0215700000	Version Accessories, Socket
	, , ,	

### **Mounting support**



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

#### **General ordering data**

Туре	BFSC M2.5X18 PA/RT	Version
Order No.	0303300000	Mounting screw (Terminal), 2.50 mm, Polyamide 66, Depth: 3.8 mm,
GTIN (EAN)	4008190040673	Width: 4.5 mm, Height: 18 mm
Qty.	100 ST	

#### Warning cover



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

#### **General ordering data**

Туре	AD 4 AKZ4	Version
Order No.	0303400000	Terminal cover, yellow, PVC, Height: 24.2 mm, Width: 20 mm, Depth:
GTIN (EAN)	4008190068158	1 mm, V-2
Qty.	50 ST	

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

Туре	DEK 5/6 MC SDR
Order No.	1609830000
GTIN (EAN)	4008190456603
Qty.	200 ST

Version

Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00

Weidmueller, To customer specification

#### **Blank**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

Type	DEK 5/6 MC NE WS	Version
Order No.	1609820000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmueller, white
Qty.	1000 ST	

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

#### General ordering data

Type QB 75/6.2/9/WI Order No. 0526400000 GTIN (EAN) 4008190099923 Qty. 10 ST

Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 75, Pitch in mm (P): 6.00, Insulated: No, Width: 0.8 mm

Version

#### **End plates and partition plates**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

### **General ordering data**

 Type
 AP DK4
 Version

 Order No.
 0359260000
 End plate for terminals, beige, Height: 50 mm, Width: 1.5 mm, V-2,

 GTIN (EAN)
 4008190012991
 PA 66, Snap-on: Yes

 Otv.
 20 ST

### **End bracket**









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### **General ordering data**

Type EW 35 Version

Order No. 0383560000 End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C GTIN (EAN) 4008190181314

Qty. 50 ST

Creation date 04.11.2025 07:01:03 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

 Type
 EWK 1
 Version

 Order No.
 0206160000
 End bracket, beige, TS 32, V-0, Wemid, Width: 9 mm, 100 °C

GTIN (EAN) 4008190080020

Qty. 50 ST

#### **End plates and partition plates**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

#### **General ordering data**

 Type
 TSCH 4 AKZ4
 Version

 Order No.
 0363360000
 Small partition (terminal), PA 66, beige, Continuous operating temp.,

 GTIN (EAN)
 4008190136680
 max.: 100 °C

 Oty.
 100 ST

#### **Mounting support**



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## **General ordering data**

 Type
 BFSC M2.5X14 SAKD2.5N
 Version

 Order No.
 0266800000
 Mounting screw (Terminal), 2.50 mm, Depth: 3.8 mm, Width: 4.5

 GTIN (EAN)
 4008 190084899
 mm, Height: 14 mm

 Qty.
 100 ST

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

#### **General ordering data**

Туре	ISPF QB75 SW	Version
Order No.	0526700000	Insulation profile, Plastic, black
GTIN (EAN)	4008190093723	
Qty.	10 ST	
Туре	VH 10/4/2.8 AKZ4	Version
Order No.	0446600000	Connecting sleeve (terminal), when screwed in, Width: 4 mm, Height:
GTIN (EAN)	4008190176211	4 mm, Depth: 10, Number of poles: 1, Cu Zn
Qty.	50 ST	
Туре	QB 75/6.2/15	Version
Order No.	0535200000	Cross-connector (terminal), when screwed in, grey, 27 A, Number of
GTIN (EAN)	4008190179168	poles: 75, Pitch in mm (P): 6.00, Insulated: No, Width: 0.8 mm
Qty.	10 ST	

### **Mounting support**



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## **General ordering data**

Туре	KISC M3X15/6 SAK2.5	Version
Order No.	0359000000	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190061548	
Qty.	100 ST	

Creation date 04.11.2025 07:01:03 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Testadapter and testsockets**









Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

#### **General ordering data**

Туре	STB 8.5/D4.5/2/M3 SAKT4	Version
Order No.	0244600000	SAK Series, Socket
GTIN (EAN)	4008190103828	
Qty.	50 ST	
Туре	STB 8.5/5/2.3/M3 SAK2.5	Version
Type Order No.	STB 8.5/5/2.3/M3 SAK2.5 0280600000	Version Accessories, Socket

### **Disconnect plugs**



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## **General ordering data**

Туре	ISPF QB75 BL	Version
Order No.	0526780000	Insulation profile, Plastic, blue
GTIN (EAN)	4008190093105	
Qty.	10 ST	
Туре	ISPF QB75 RT	Version
Type Order No.	ISPF QB75 RT 0526760000	Version Insulation profile, Plastic, red

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Mounting support**



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

#### General ordering data

Туре	IH 2.8 DB	Version
Order No.	0386060000	W-Series, Insulating sleeve
GTIN (EAN)	4008190043414	
Qty.	100 ST	
Туре	IH 6.3 WEM GE	Version
Order No.	0386260000	
Oluei No.	0380200000	W-Series, Insulating sleeve
GTIN (EAN)	4008190164256	W-Series, Insulating sleeve

### **End plates and partition plates**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

### **General ordering data**

Туре	AP DK4S	Version
Order No.	0631360000	End plate for terminals, beige, Height: 54 mm, Width: 1.5 mm, V-2,
GTIN (EAN)	4008190101329	PA 66, Snap-on: Yes
Qty.	20 ST	
Туре	AP DK4 BL	Version
Order No.	0359280000	End plate for terminals, blue, Height: 50 mm, Width: 1.5 mm, V-2, PA
GTIN (EAN)	4008190031213	66, Snap-on: Yes
Qty.	20 ST	
Туре	AP DK4/380 Q	Version
Order No.	0438560000	End plate for terminals, beige, Height: 51 mm, Width: 1.5 mm, V-2,
GTIN (EAN)	4008190133351	PA 66, Snap-on: Yes
Qty.	20 ST	
Qty.	20 \$1	

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### Warning cover



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

#### General ordering data

 Type
 AD 3 SAK2.5
 Version

 Order No.
 0297900000
 Terminal cover, yellow, PVC, Height: 24 mm, Width: 18 mm, Depth: 1

 GTIN (EAN)
 4008190038229
 mm, V-2

 Oty.
 50 ST

#### **End plates and partition plates**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

### **General ordering data**

Туре	WAP WDK2.5	Version
Order No.	<u>1059100000</u>	End plate for terminals, dark beige, Height: 69 mm, Width: 1.5 mm,
GTIN (EAN)	4008190101954	V-0, Wemid, Snap-on: No
Qty.	20 ST	

### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Creation date 04.11.2025 07:01:03 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

General of	ordering	data
------------	----------	------

Туре	DEK 5/6 MC NE BL	Version
Order No.	1238290000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118267327	Weidmueller, blue
Qty.	1000 ST	
Туре	DEK 5/6 MC NE BR	Version
Order No.	1454900000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118323313	Weidmueller, brown
Qty.	1000 ST	
Туре	DEK 5/6 MC NE GE	Version
Order No.	<u>1238280000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118038750	Weidmueller, yellow
Qty.	1000 ST	
Туре	DEK 5/6 MC NE GN	Version
Order No.	<u>1238310000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118271812	Weidmueller, green
Qty.	1000 ST	
Туре	DEK 5/6 MC NE GR	Version
Order No.	1238330000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118323306	Weidmueller, grey
Qty.	1000 ST	
Туре	DEK 5/6 MC NE OR	Version
Order No.	<u>1912090000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4032248540525	Weidmueller, orange
	4032246540525	Welating Country Count
Qty.	1000 ST	vveidindenei, ordinge

#### Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

17

### **General ordering data**

Туре	DEK 5/6 PLUS MC NE WS	Version
Order No.	<u>1011320000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4032248717644	Weidmueller, white
Qty.	1000 ST	



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

#### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

Type DEK 5/6 PLUS MC SDR
Order No. 1038650000
GTIN (EAN) 4032248767908

200 ST

Version

Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00

Weidmueller, To customer specification

#### **DEK 5/6**

Qty.



#### WS/DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- · Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

#### **General ordering data**

Туре	DEK 5/6 MM WS	Version
Order No.	2007120000	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 ST	

Creation date 04.11.2025 07:01:03 MEZ





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

#### **General ordering data**

Туре	BZT 1 WS 10/5	Version
Order No.	1805490000	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Туре	DZT 1 ZA W/C 10 /F	Version
Type	BZT 1 ZA WS 10/5	version
Order No.	1805520000	Accessories, Marker holder
	,	