

## CLI O 20-3 GE/SW + MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers. Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 3 - 4 mm, 3 x 5.5 mm, yellow |
| Order No.  | <a href="#">0648101738</a>   |
| Type       | CLI O 20-3 GE/SW + MP  |
| GTIN (EAN) | 4032248455317  |
| Qty.       | 200 items  |

## CLI O 20-3 GE/SW + MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5 mm   | Depth (inches)  | 0.1968 inch |
| Height     | 3 mm   | Height (inches) | 0.1181 inch |
| Width      | 5.5 mm | Width (inches)  | 0.2165 inch |
| Net weight | 0.03 g |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|  |                    |                                   |                            |
|--|--------------------|-----------------------------------|----------------------------|
| Material colour according to resistance code | 4                  | Orientation of print              | horizontal                 |
| Type of printing                             | Standard           | Printing method                   | hot-embossing              |
| Version                                      | MultiPack          | Width                             | 5.5 mm                     |
| UL 94 flammability rating                    | V-0                | Operating temperature range, max. | 80 °C                      |
| Operating temperature range, min.            | -30 °C             | Colour                            | yellow                     |
| Halogen                                      | Yes                | Basic material                    | PVC, soft, without Cadmium |
| Colour of printing                           | black              | Printed characters                | Symbols                    |
| Recommended industries                       | Process, Machinery | Operating temperature range       | -30...80 °C                |
| Imprint                                      | +                  |                                   |                            |

### Conductor and cable markers

|                                  |                         |                               |                   |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen                          | Yes                     | Conductor cross-section, max. | 3 mm <sup>2</sup> |
| Conductor cross-section, min.    | 1.5 mm <sup>2</sup>     | Conductor O.D., max.          | 4 mm              |
| Conductor O.D., min.             | 3 mm                    | Conductor O.D.                | 3 - 4 mm          |
| Cross-section for connected wire | 1.5 - 3 mm <sup>2</sup> |                               |                   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |



Similar to illustration