


**SLS 5.08/12/180F SN SW BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

**General ordering data**

|              |                                                                                                                                      |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 12, 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², Box |
| Order No.    | <a href="#">1000850001</a>                                                                                                           |
| Type         | SLS 5.08/12/180F SN SW BX                                                                                                            |
| GTIN (EAN)   | 4032248691241                                                                                                                        |
| Qty.         | 24 items                                                                                                                             |
| Product data | IEC: 400 V / 21.5 A / 0.2 - 2.5 mm²<br>UL: 300 V / 14 A / AWG 26 - AWG 12                                                            |
| Packaging    | Box                                                                                                                                  |

## SLS 5.08/12/180F SN SW BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 22.2 mm | Depth (inches)  | 0.874 inch  |
| Height     | 15.3 mm | Height (inches) | 0.6024 inch |
| Net weight | 10.66 g |                 |             |

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP 5f72207e-da7b-4e67-98e6-158600cbc2d0

## System Parameters

|                                              |                                                  |                   |                            |
|----------------------------------------------|--------------------------------------------------|-------------------|----------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08              |                   |                            |
| Type of connection                           | Field connection                                 |                   |                            |
| Wire connection method                       | Clamping yoke connection                         |                   |                            |
| Pitch in mm (P)                              | 5.08 mm                                          |                   |                            |
| Pitch in inches (P)                          | 0.200 "                                          |                   |                            |
| Conductor outlet direction                   | 180°                                             |                   |                            |
| Number of poles                              | 12                                               |                   |                            |
| L1 in mm                                     | 55.88 mm                                         |                   |                            |
| L1 in inches                                 | 2.200 "                                          |                   |                            |
| Number of rows                               | 1                                                |                   |                            |
| Pin series quantity                          | 1                                                |                   |                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe plugged/ back-of-hand-safe unplugged |                   |                            |
| Touch-safe protection acc. to DIN VDE 0470   | IP20 plugged/ IP10 unplugged                     |                   |                            |
| Protection degree                            | IP20, when fully mounted                         |                   |                            |
| Volume resistance                            | ≤5 mΩ                                            |                   |                            |
| Can be coded                                 | Yes                                              |                   |                            |
| Stripping length                             | 7 mm                                             |                   |                            |
| Clamping screw                               | M 2.5                                            |                   |                            |
| Screwdriver blade                            | 0.6 x 3.5                                        |                   |                            |
| Screwdriver blade standard                   | DIN 5264-A                                       |                   |                            |
| Plugging cycles                              | 25                                               |                   |                            |
| Plugging force/pole, max.                    | 4 N                                              |                   |                            |
| Pulling force/pole, max.                     | 3 N                                              |                   |                            |
| Tightening torque                            | Torque type                                      | Wire connection   |                            |
|                                              | Usage information                                | Tightening torque | min. 0.4 Nm<br>max. 0.5 Nm |

## SLS 5.08/12/180F SN SW BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Material data

|                                       |          |                                       |                            |
|---------------------------------------|----------|---------------------------------------|----------------------------|
| Insulating material                   | PBT      | Colour                                | black                      |
| Colour chart (similar)                | RAL 9011 | Insulating material group             | IIIa                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Moisture Level (MSL)                  |                            |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-alloy                   |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C                     |

## Conductors suitable for connection

|                                                                     |                         |
|---------------------------------------------------------------------|-------------------------|
| Clamping range, min.                                                | 0.13 mm <sup>2</sup>    |
| Clamping range, max.                                                | 3.31 mm <sup>2</sup>    |
| Wire connection cross section AWG, min.                             | AWG 26                  |
| Wire connection cross section AWG, max.                             | AWG 12                  |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>     |
| Solid, max. H05(07) V-U                                             | 2.5 mm <sup>2</sup>     |
| Stranded, min. H07V-R                                               | 0.2 mm <sup>2</sup>     |
| Stranded, max. H07V-R                                               | 2.5 mm <sup>2</sup>     |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>     |
| Flexible, max. H05(07) V-K                                          | 2.5 mm <sup>2</sup>     |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                         |
| w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm <sup>2</sup> max. |                         |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>     |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 2.5 mm <sup>2</sup>     |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.8 mm x 2.0 mm; 2.4 mm |

|                     |                                        |                              |                        |      |
|---------------------|----------------------------------------|------------------------------|------------------------|------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired             |      |
|                     |                                        | nominal                      | 0.5 mm <sup>2</sup>    |      |
|                     | wire end ferrule                       | Stripping length             | nominal                | 6 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a> |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired             |      |
|                     |                                        | nominal                      | 1 mm <sup>2</sup>      |      |
|                     | wire end ferrule                       | Stripping length             | nominal                | 6 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a> |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired             |      |
|                     |                                        | nominal                      | 1.5 mm <sup>2</sup>    |      |
|                     | wire end ferrule                       | Stripping length             | nominal                | 7 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a> |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired             |      |
|                     |                                        | nominal                      | 2.5 mm <sup>2</sup>    |      |
|                     | wire end ferrule                       | Stripping length             | nominal                | 7 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H2.5/7</a> |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired             |      |
|                     |                                        | nominal                      | 0.75 mm <sup>2</sup>   |      |
|                     | wire end ferrule                       | Stripping length             | nominal                | 6 mm |

## SLS 5.08/12/180F SN SW BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Recommended wire-  
end ferrule [H0.75/6](#)

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage.

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 21.5 A            |
| Rated current, max. number of poles (Tu=20°C)                             | 16 A                   | Rated current, min. number of poles (Tu=40°C)                         | 18 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 14 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 15 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 26 | Wire cross-section, AWG, max.     | AWG 12 |

## Rated data acc. to UL 1059

|                                       |                                                                        |                                       |        |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (UR)                        | UR                                                                     | Certificate No. (UR)                  | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V                                                                  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 14 A                                                                   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26                                                                 | Wire cross-section, AWG, max.         | AWG 12 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

## Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 349.00 mm |
| VPE width | 141.00 mm | VPE height | 31.00 mm  |

## Type tests

|                               |                |                                               |           |
|-------------------------------|----------------|-----------------------------------------------|-----------|
| Test: Durability of markings  | Standard       | VDE 0627 Tab. 7 item 3/6.86                   |           |
|                               | Test           | durability                                    |           |
|                               | Evaluation     | passed                                        |           |
| Test: Clampable cross section | Standard       | VDE 0609 part 1 06.83, EN 60947-1 03.91       |           |
|                               | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|                               |                | Type of conductor and conductor cross-section | H05V-K0.5 |
|                               |                | Type of conductor and conductor cross-section | H05V-U2.5 |
|                               |                | Type of conductor and conductor cross-section | H05V-K2.5 |

## Technical data

|                                                           |                |                                               |           |
|-----------------------------------------------------------|----------------|-----------------------------------------------|-----------|
| Test for damage to and accidental loosening of conductors |                | Type of conductor and conductor cross-section | AWG 28    |
|                                                           |                | Type of conductor and conductor cross-section | AWG 14    |
|                                                           | Evaluation     | passed                                        |           |
|                                                           | Standard       | EN 60947-1/1991 section 8.2.4.3               |           |
|                                                           | Requirement    | 0.3 kg                                        |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|                                                           |                | Type of conductor and conductor cross-section | H05V-K0.5 |
|                                                           | Evaluation     | passed                                        |           |
|                                                           | Requirement    | 0.7 kg                                        |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | H07V-U2.5 |
|                                                           |                | Type of conductor and conductor cross-section | H07V-K2.5 |
| Pull-out test                                             | Evaluation     | passed                                        |           |
|                                                           | Standard       | EN 60947-1/1991 section 8.2.4.4               |           |
|                                                           | Requirement    | ≥5 N                                          |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | AWG 28/1  |
|                                                           |                | Type of conductor and conductor cross-section | AWG 28/7  |
|                                                           | Evaluation     | passed                                        |           |
|                                                           | Requirement    | ≥50 N                                         |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | H07V-U2.5 |
|                                                           |                | Type of conductor and conductor cross-section | H07V-K2.5 |
|                                                           |                | Type of conductor and conductor cross-section | AWG 14/19 |
|                                                           | Evaluation     | passed                                        |           |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                           |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                |
| Notes          | <ul style="list-style-type: none"> <li>In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Classifications

|          |          |          |          |
|----------|----------|----------|----------|
| ETIM 6.0 | EC002638 | ETIM 7.0 | EC002638 |
| ETIM 8.0 | EC002638 | ETIM 9.0 | EC002638 |

## SLS 5.08/12/180F SN SW BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data


|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 10.0   | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |
| ECLASS 13.0 | 27-46-02-02 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |

## Drawings


### Product image




### Dimensional drawing



### Graph



### Graph



### Graph

