

WSMH 176MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

Version	Stainless steel markers, Conductor and cable markers, 14 - 79 mm, 176 x 11 mm, silver
Order No.	1002680000
Type	WSMH 176MM
GTIN (EAN)	4032248695102
Qty.	50 items

WSMH 176MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.0118 inch
Height	176 mm	Height (inches)	6.9291 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	2.4 g		

Temperatures

Operating temperature range 250 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Number per sheet	50
Type of printing	neutral
Width	11 mm
Operating temperature range, max.	250 °C
Colour	silver
Basic material	Stainless steel 1.4404
Printed characters	without
Number of characters	28
Number of markers per packaging unit	Form of supply Component part
Number of markers per combination	1 Component part = Conductor and cable markers
Operating temperature range	250 °C

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Conductor O.D., max.	79 mm	Conductor O.D., min.	14 mm
Conductor O.D.	14 - 79 mm	Cross-section for connected wire	16 - 500 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		