

KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Ideally suited for the energy, process and transportation industries, the Klippon® STB enclosure series is the perfect complement to our existing Klippon® enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. EN62208 and EN60079-0/7 (ATEX).

- Mirror-polished or electropolished stainless steel 1.4404 (316L), 1.5 mm
- High-temperature-resistant seal as standard - extended temperature range of -60°C to +100°C for Ex application (+120°C only for industrial application)
- Approved according to ATEX, IECEx, cULus, Lloyds Register, Germanischer Lloyd, GL DNV and INMETRO
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Klippon STB (Small Terminal Box), Empty enclosure, stainless steel enclosure, Height: 150 mm, Width: 120 mm, Depth: 80 mm, Basic material: Stainless steel 1.4404 (316L), Mirror polished, silver
Order No.	1002750000
Type	KLIPPON STB 1.1 SS
GTIN (EAN)	4032248695683
Qty.	1 items

KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E197061

Dimensions and weights

Depth	80 mm	Depth (inches)	3.1496 inch
Height	150 mm	Height (inches)	5.9055 inch
Width	120 mm	Width (inches)	4.7244 inch
Mounting dimension - width	145 mm	Net weight	1451 g

Temperatures

Operating temperature	-60 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Cable glands, left

M12	10	M16	6
M32	2	M25	2
M20	6	M40	1

Cable glands, right

M25	2	M16	6
M40	1	M32	2
M20	6	M12	10

Cable glands, top/bottom

M20	6	M12	10
M40	2	M32	2
M25	3	M16	6

Certificate numbers enclosure

Declaration of Conformatiy No. (DoC LVD)	DE PS2620 160412 001ISS02	Attestation of Conformatiy No. (AoC)	DE PS2620 160308 001ISS04
Certificate no. Terminal Box (KOSHA)	16-AV4BO-0247X	Certificate no. empty enclosure (INMETRO)	LMP 21.0015U
Certificate No. (DNV)	TAE00003ZT	Certificate no. Terminal Box (AEx)	E223792
Certificate no. Terminal Box (ATEX)	IBExU07ATEX1148	Certificate no. empty enclosure (ATEX)	IBExU 07ATEX1147U

KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Certificate No. (LLOYDSREG)	LR23307703TA	Certificate no. Terminal Box (INMETRO)	LMP 21.0018
Certificate no. (INMETRO)	IEX13.0003	Certificate no. Terminal Box (IECEX)	IECEX IBE 09.0019
Certificate no. empty enclosure (IECEX)	IECEX IBE 09.0018U	Certificate No. (IECEX)	IECEXIBE09.0018U
Certificate No. (ATEX)	IBEXU07ATEX1147U	Approval conditions	ATEX, DNV, IECEX, INMETRO, LR, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus, KC, CCC
Certificate no. (cULus)	E197061		

General information

Material thickness of cover	1.5 mm	Material thickness of enclosure	1.5 mm
Operating temperature, max.	100 °C	Operating temperature, min.	-60 °C
Lid attachment	M5 hexagonal screw with slot and 10mm distance across flats	Surface finish	Mirror polished
Impact resistance	10 J version standard, 7 J ATEX version	Protection degree	IP66
Basic material	Stainless steel 1.4404 (316L)	Seal material	Silicone
Torque for lid screws	2.5 Nm	Integral fixing	TAS 20 rail welded to floor
Enclosure attachment	Welded-on mounting foot with 8-mm holes	Protection class (UL)	Type 4, Type 4X
Number of lid screws	4	Access opening: width	100 mm
Flange plate	No	Lid	Yes
Access opening: height	132 mm	Areas of use	Explosive risk zone, Packaging industry, Transportation, Process industry, Marine engineering

Housing earth

Cross-section , max.	25 mm ²	Earth, enclosure, cover	Welded-on M6 x 10 stainless-steel earth stud
Earth, enclosure, external	Welded-on M6 x 16 stainless-steel bolts	Earth, enclosure, internal	Welded-on M6 x 16 stainless-steel bolts

vertical assembly

WDU 10 / ZDU 10	1x11	WDU 16 / ZDU 16	1x9
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x23	WDU 4 / ZDU 4	1x19
WDU 6 / ZDU 6	1x14		

Important note

Product information The ambient temperature for the assembly will be reduced to +60°C and the surface temperature to +100°C.

Classifications

ETIM 8.0	EC002503	ETIM 9.0	EC002503
ETIM 10.0	EC002503	ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		


KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing



KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Terminal rails - TS35



The system accessories for the Klippon® STB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35
- Mounting screws

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	SFNS5 VKMU M5 SW15	Version	
Order No.	0433500000	Klippon STB (Small Terminal Box), Fixing nut, Square, Height: 15 mm,	
GTIN (EAN)	4008190494520	Width: 15 mm, Depth: 11.7 mm, Basic material: Steel, galvanized,	
Qty.	20 ST	galvanized, silver	

Installation material



Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

General ordering data

Type	TPSD FIXING SET KTB	Version	
Order No.	1252190000	Klippon TB (Terminal Box), Type plate fixings set, Basic material:	
GTIN (EAN)	4050118043969	Stainless steel, rust-proof, untreated, silver	
Qty.	20 ST		

Type	SD FIXING SET	Version	
Order No.	1285200000	Klippon TB (Terminal Box), Identification plate fixing set, Height: 12	
GTIN (EAN)	4050118075472	mm, Width: 12 mm, Depth: 16.4 mm, Basic material: Stainless steel,	
Qty.	1 ST	rust-proof, untreated, silver	

KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Grounding strap

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application. The following options are available:

- Closure Elements
- Document holders
- Earthing stud
- Gland plates
- Installation material
- Mounting plates
- Rain hoods
- Spacer
- Terminal rails
- Type label holder

General ordering data

Type	PECD WIRE 6/200/D6 SET	Version
Order No.	2475490000	Klippon TB (Terminal Box), Grounding strap, Ssrewed, Basic material:
GTIN (EAN)	4050118487206	Steel, Green/yellow
Qty.	1 ST	

Ventilation plugs - DAE



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	DAE M12 SS	Version
Order No.	1868550000	DAE (ventilation element), Compensating element, straight, M 12, 10 mm, IP66, IP68, IP69K, Stainless steel 1.4305 (303)
GTIN (EAN)	4032248440405	
Qty.	10 ST	
Type	DAE M12 PA LONG	Version
Order No.	1868570000	DAE (ventilation element), Compensating element, straight, M 12, 10 mm, IP66, IP68, IP69K, Polyamide 6
GTIN (EAN)	4032248440429	
Qty.	10 ST	

KLIPPON STB 1.1 SS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Terminal rails - TS35



The system accessories for the Klippon® STB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35
- Mounting screws

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	TS35X7.5 ST STB 1.1 STB...	Version
Order No.	8683740000	Rail, TS 35, TS 35 x 7.5, Width: 110 mm, without slot, Steel,
GTIN (EAN)	4050118652765	galvanized, chromium-plated
Qty.	20 ST	
Type	TS35X15 ST STB 1.1 STB 2	Version
Order No.	8000073218	Rail, TS 35, TS 35 x 15, Width: 110 mm, with slot, Steel, galvanic zinc
GTIN (EAN)	4064675356769	plated and passivated
Qty.	20 ST	