

HDC C HX SM4.0AG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Heavy-duty connectors, Crimp contact, MixMate, Male, Conductor cross-section, max.: 4, turned, Copper alloy
Order No.	1002930000
Type	HDC C HX SM4.0AG
GTIN (EAN)	4032248697212
Qty.	25 items

HDC C HX SM4.0AG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Diameter 6 mm Net weight 2.95 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	4 mm	Stripping length, rated connection	8 mm
Type of connection	Crimp connection	Version insert	MixMate
Volume resistance	≤1 mΩ	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	4 mm ²	Surface finish	silver
Plugging cycles	≥ 500	Type	Male
Basic material	Copper alloy	Production methods	turned
Cross-section for connected wire	4 - 4 mm ²	Material of contact	Copper alloy

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC C HX SM4.0AG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC C HX SM4.0AG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for turned contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Type	CTIN CM 1.6/2.5	Version	
Order No.	9205430000	Pressing tool, Crimping tool for contacts, 0.14mm ² , 6mm ² , 4-indent crimp	
GTIN (EAN)	4032248733446		
Qty.	1 ST		
Type	CTIN CM 3.6	Version	
Order No.	9205440000	Crimping tool for contacts, 1.5mm ² , 10mm ² , 4-indent crimp	
GTIN (EAN)	4032248734146		
Qty.	1 ST		

Contact removal tools



Weidmüller offers a variety of crimping tools, contact removal tools, and fibre optic tools.

General ordering data

Type	REMOVAL TOOL HX	Version	
Order No.	1002990000		
GTIN (EAN)	4032248697274		
Qty.	1 ST		

2-pole



The HQ series - big features in a compact design. The electrical characteristics speak for themselves. The wire connection level is designed for crimp contacts. The proven crimp connection method has been in standard use for decades. Crimp contacts are not included in the scope of delivery of inserts.

HDC C HX SM4.0AG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	HDC HQ 2 FC	Version
Order No.	3103510000	HDC insert, Female, 400 V, 40 A, Number of poles: 2, Crimp contact,
GTIN (EAN)	4099987 151238	Installation size: 1
Qty.	1 ST	
Type	HDC HQ 2 MC	Version
Order No.	3103500000	HDC insert, Male, 400 V, 40 A, Number of poles: 2, Crimp contact,
GTIN (EAN)	4099987 151221	Installation size: 1
Qty.	1 ST	

3-pole



The HQ series - big features in a compact design. The electrical characteristics speak for themselves. The wire connection level is designed for crimp contacts. The proven crimp connection method has been in standard use for decades. Crimp contacts are not included in the scope of delivery of inserts.

General ordering data

Type	HDC HQ 3 FC	Version
Order No.	3103530000	HDC insert, Female, 400 V, 40 A, Number of poles: 3, Crimp contact,
GTIN (EAN)	4099987 151252	Installation size: 1
Qty.	1 ST	
Type	HDC HQ 3 MC	Version
Order No.	3103520000	HDC insert, Male, 400 V, 40 A, Number of poles: 3, Crimp contact,
GTIN (EAN)	4099987 151245	Installation size: 1
Qty.	1 ST	

4-pole



The HQ series - big features in a compact design. The electrical characteristics speak for themselves. The wire connection level is designed for crimp contacts. The proven crimp connection method has been in standard use for decades. Crimp contacts are not included in the scope of delivery of inserts.

General ordering data

Type	HDC HQ 4 FC	Version
Order No.	3103550000	HDC insert, Female, 830 V, 40 A, Number of poles: 4, Crimp contact,
GTIN (EAN)	4099987 151559	Installation size: 1
Qty.	1 ST	
Type	HDC HQ 4 MC	Version
Order No.	3103540000	HDC insert, Male, 830 V, 40 A, Number of poles: 4, Crimp contact,
GTIN (EAN)	4099987 151283	Installation size: 1
Qty.	1 ST	

HDC C HX SM4.0AG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

4/2-pole



The HQ series - big features in a compact design. The electrical characteristics speak for themselves. You can also use the proven HD and HX crimp contacts here. The wire connection level is designed for crimp contacts. The proven crimp connection has been in standard use for decades. Crimp contacts are not included in the scope of delivery of inserts.
 Pole count: 4/2 (+PE)
 Rated current: 40/10 A
 Rated voltage: 690 / 250 V
 Rated voltage acc. to UL/CSA: 600 V AC/DC

General ordering data

Type	HDC HQ 4/2 FC	Version
Order No.	1003160000	HDC insert, Female, 690 V, 40 A, Number of poles: 6, Crimp connection, Installation size: HQ
GTIN (EAN)	4032248698158	
Qty.	1 ST	
Type	HDC HQ 4/2 MC	Version
Order No.	1003170000	HDC insert, Male, 690 V, 40 A, Number of poles: 6, Crimp connection, Installation size: HQ
GTIN (EAN)	4032248698165	
Qty.	1 ST	