

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The HQ series - big features in a compact design. The electrical characteristics speak for themselves. You can also use the proven HD and HX crimp contacts here. The wire connection level is designed for crimp contacts. The proven crimp connection has been in standard use for decades.

Crimp contacts are not included in the scope of delivery of inserts.

Pole count: 4/2 (+PE)

Rated current: 40/10 A

Rated voltage: 690 / 250 V

Rated voltage acc. to UL/CSA: 600 V AC/DC

General ordering data

| | |
|------------|--|
| Version | HDC insert, Female, 690 V, 40 A, Number of poles: 6, Crimp connection, Installation size: HQ |
| Order No. | 1003160000 |
| Type | HDC HQ 4/2 FC |
| GTIN (EAN) | 4032248698158 |
| Qty. | 1 items |

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 41.6 mm | Depth (inches) | 1.6378 inch |
| Height | 39.8 mm | Height (inches) | 1.5669 inch |
| Width | 22.4 mm | Width (inches) | 0.8819 inch |
| Net weight | 13.2 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------------------|--|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | 1609748e-c278-4c9b-b3d1-e6215d2988cd |

| | | |
|---------------------|--------------------------|---------------------------|
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Resistant |
| | Substance | Ammonia, watery |
| | Chemical resistance | Conditionally resistant |
| | Substance | Petrol |
| | Chemical resistance | Resistant |
| | Substance | Benzene |
| | Chemical resistance | Resistant |
| | Substance | Diesel oil |
| | Chemical resistance | Conditionally resistant |
| | Substance | Acetic acid, concentrated |
| | Chemical resistance | Resistant |
| | Substance | Potassium hydroxide |
| | Chemical resistance | Conditionally resistant |
| | Substance | Methanol |
| | Chemical resistance | Conditionally resistant |
| | Substance | Motor oil |
| | Chemical resistance | Conditionally resistant |
| | Substance | Lye, diluted |
| | Chemical resistance | Resistant |
| Substance | Hydrochlorofluorocarbons | |
| Chemical resistance | Conditionally resistant | |
| Substance | Outdoor use | |
| Chemical resistance | Conditionally resistant | |

Dimensions

| | | | |
|------------------|---------|-------------------|---------|
| Width | 22.4 mm | Total length base | 41.6 mm |
| Height of socket | 39.8 mm | | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General data

| | | | |
|-----------------------------------|--------------|--------------------------------------|---|
| Number of poles | 6 | Plugging cycles, silver | ≥ 500 |
| Plugging cycles, gold | ≥ 500 | Type of connection | Crimp connection |
| Installation size | HQ | UL 94 flammability rating | V-0 |
| Volume resistance | ≤1 mΩ, ≤4 mΩ | Colour | beige |
| Insulation resistance | 1010 Ω | Insulating material | PC glass-fibre reinforced (UL-listed and railway-certified) |
| Insulating material group | IIIa | Type | Female |
| Pollution severity | 3 | Basic material | Copper alloy |
| Series | HQ | Rated voltage (DIN EN 61984) | 690 V |
| Rated voltage according to UL/CSA | 600 V AC/DC | Rated impulse voltage (DIN EN 61984) | 6 kV |
| Rated current (DIN EN 61984) | 40 A | Free from halogens | false |
| Low smoke acc. DIN EN 45545-2 | Yes | BG | HQ |
| Number of signal contacts | 2 | Signal contact, type | HD |
| Number of power contacts | 4 | Power contact, type | HX |

Connection data PE

| | | | |
|------------------------------------|-------------------|------------------------------------|--------|
| Connection type PE | Crimp connection | Stripping length PE connection | 9 mm |
| Rated cross-section | 6 mm ² | Wire cross section, AWG (PE), min. | AWG 16 |
| Wire cross section, AWG (PE), max. | AWG 8 | | |

Power contact

| | | |
|---|-----------------------------------|--------|
| Type of connection, power contact | Crimp connection | |
| Number of poles, performance contact | 4 | |
| Stripping length, performance contact | 9 mm | |
| Clamping range, power contact, max. | 6 mm ² | |
| Clamping range, power contact, min. | 1.5 mm ² | |
| Rated voltage (DIN EN 61984), power contact | 690 V | |
| Rated impulse voltage (DIN EN 61984), power contact | 6 kV | |
| Rated current (DIN EN 61984), power contact | 40 A | |
| Rated current power circuit (UR) | Wire connection cross section AWG | AWG 10 |
| | Rated current | 40 A |
| | Wire connection cross section AWG | AWG 12 |
| | Rated current | 20 A |
| | Wire connection cross section AWG | AWG 14 |
| | Rated current | 15 A |
| Rated current signal circuit (UR) | Wire connection cross section AWG | AWG 16 |
| | Rated current | 10 A |
| | Wire connection cross section AWG | AWG 14 |
| | Rated current | 15 A |
| | Wire connection cross section AWG | AWG 16 |
| | Rated current | 10 A |
| Rated current signal circuit (cUR) | Wire connection cross section AWG | AWG 18 |
| | Rated current | 7 A |
| | Wire connection cross section AWG | AWG 20 |
| | Rated current | 5 A |
| | Wire connection cross section AWG | AWG 22 |
| | Rated current | 3 A |
| Rated current signal circuit (cUR) | Wire connection cross section AWG | AWG 14 |
| | Rated current | 10.5 A |
| | Wire connection cross section AWG | AWG 16 |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | |
|-----------------------------------|-----------------------------------|--------|
| | Rated current | 8.2 A |
| | Wire connection cross section AWG | AWG 18 |
| | Rated current | 6.8 A |
| | Wire connection cross section AWG | AWG 20 |
| | Rated current | 5.7 A |
| | Wire connection cross section AWG | AWG 22 |
| | Rated current | 4.3 A |
| Rated current power circuit (cUR) | Wire connection cross section AWG | AWG 10 |
| | Rated current | 30 A |
| | Wire connection cross section AWG | AWG 12 |
| | Rated current | 25 A |
| | Wire connection cross section AWG | AWG 14 |
| | Rated current | 18 A |
| | Wire connection cross section AWG | AWG 16 |
| | Rated current | 14 A |

Signal contact

| | | | |
|--|------------------------------------|-----------------------------------|--------|
| Type of connection, signal | Crimp connection | | |
| Number of poles, signal | 2 | | |
| Clamping range, signal contact, max. | 2.5 mm ² | | |
| Clamping range, signal contact, min. | 0.14 mm ² | | |
| Stripping length, signal | 8 mm | | |
| Rated voltage (DIN EN 61984), signal contact | 250 V | | |
| Rated impulse voltage (DIN EN 61984), signal | 4 kV | | |
| Rated current (DIN EN 61984), signal | 10 A | | |
| Rated current power circuit (UR) | Wire connection cross section AWG | AWG 10 | |
| | Rated current | 40 A | |
| | Wire connection cross section AWG | AWG 12 | |
| | Rated current | 20 A | |
| | Wire connection cross section AWG | AWG 14 | |
| | Rated current | 15 A | |
| | Wire connection cross section AWG | AWG 16 | |
| | Rated current | 10 A | |
| Rated current signal circuit (UR) | Wire connection cross section AWG | AWG 14 | |
| | Rated current | 15 A | |
| | Wire connection cross section AWG | AWG 16 | |
| | Rated current | 10 A | |
| | Wire connection cross section AWG | AWG 18 | |
| | Rated current | 7 A | |
| | Wire connection cross section AWG | AWG 20 | |
| | Rated current | 5 A | |
| | Wire connection cross section AWG | AWG 22 | |
| | Rated current | 3 A | |
| | Rated current signal circuit (cUR) | Wire connection cross section AWG | AWG 14 |
| | | Rated current | 10.5 A |
| Wire connection cross section AWG | | AWG 16 | |
| Rated current | | 8.2 A | |
| Wire connection cross section AWG | | AWG 18 | |
| Rated current | | 6.8 A | |
| Wire connection cross section AWG | | AWG 20 | |
| Rated current | | 5.7 A | |
| Wire connection cross section AWG | | AWG 22 | |
| Rated current | | 4.3 A | |
| Rated current power circuit (cUR) | | Wire connection cross section AWG | AWG 10 |
| | | Rated current | 30 A |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | |
|-----------------------------------|--------|
| Wire connection cross section AWG | AWG 12 |
| Rated current | 25 A |
| Wire connection cross section AWG | AWG 14 |
| Rated current | 18 A |
| Wire connection cross section AWG | AWG 16 |
| Rated current | 14 A |

Version

| | | | |
|--|-------------------|--|---------------------|
| Wire connection cross section AWG, max. | AWG 8 | Stripping length, rated connection | 9 mm |
| Type of connection | Crimp connection | Installation size | HQ |
| Volume resistance | ≤1 mΩ, ≤4 mΩ | Wire connection cross section AWG, min. | AWG 16 |
| Wire connection cross section, finely stranded, max. | 6 mm ² | Wire connection cross section, finely stranded, min. | 1.5 mm ² |
| Conductor cross-section, max. | 6 mm ² | Conductor cross-section, min. | 1.5 mm ² |
| Basic material | Copper alloy | BG | HQ |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000438 | ETIM 9.0 | EC000438 |
| ETIM 10.0 | EC000438 | ECLASS 14.0 | 27-44-02-05 |
| ECLASS 15.0 | 27-44-02-05 | | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

| | | | |
|------------|----------------------------|--------------------------|--|
| Type | SDIS 0.6X3.5X100 | Version | |
| Order No. | 9008390000 | Screwdriver, Screwdriver | |
| GTIN (EAN) | 4032248056354 | | |
| Qty. | 1 ST | | |

| | | | |
|------------|----------------------------|--------------------------|--|
| Type | SDS 0.6X3.5X100 | Version | |
| Order No. | 9008330000 | Screwdriver, Screwdriver | |
| GTIN (EAN) | 4032248056286 | | |
| Qty. | 1 ST | | |

Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

| | | | |
|------------|----------------------------|--------------------------|--|
| Type | SDIK PH0 | Version | |
| Order No. | 9008560000 | Screwdriver, Screwdriver | |
| GTIN (EAN) | 4032248056552 | | |
| Qty. | 1 ST | | |

| | | | |
|------------|----------------------------|--------------------------|--|
| Type | SDK PH0 | Version | |
| Order No. | 9008470000 | Screwdriver, Screwdriver | |
| GTIN (EAN) | 4032248056460 | | |
| Qty. | 1 ST | | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for turned contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | CTIN CM 1.6/2.5 | Version | |
| Order No. | 9205430000 | Pressing tool, Crimping tool for contacts, 0.14mm ² , 6mm ² , 4-indent | |
| GTIN (EAN) | 4032248733446 | crimp | |
| Qty. | 1 ST | | |

Contact removal tools



Weidmüller offers a variety of crimping tools, contact removal tools, and fibre optic tools.

General ordering data

| | | | |
|------------|----------------------------|-----------------------------|--|
| Type | REMOVAL TOOL HD | Version | |
| Order No. | 1866730000 | Tools, Contact Removal Tool | |
| GTIN (EAN) | 4032248437054 | | |
| Qty. | 1 ST | | |

Crimp contacts HX



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | HDC C HX BM1.5AG | Version | |
| Order No. | 1002950000 | Heavy-duty connectors, Crimp contact, MixMate, Female, Conductor | |
| GTIN (EAN) | 4032248697236 | cross-section, max.: 1.5, turned, Copper alloy | |
| Qty. | 25 ST | | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | HDC C HX BM2.5AG | Version |
| Order No. | 1002960000 | Heavy-duty connectors, Crimp contact, MixMate, Female, Conductor |
| GTIN (EAN) | 4032248697243 | cross-section, max.: 2.5, turned, Copper alloy |
| Qty. | 25 ST | |
| Type | HDC C HX BM4.0AG | Version |
| Order No. | 1002970000 | Heavy-duty connectors, Crimp contact, HQ, MixMate, Female, |
| GTIN (EAN) | 4032248697250 | Conductor cross-section, max.: 4, turned, Copper alloy |
| Qty. | 25 ST | |
| Type | HDC C HX BM6.0AG | Version |
| Order No. | 1002980000 | Heavy-duty connectors, Crimp contact, MixMate, Female, Conductor |
| GTIN (EAN) | 4032248697267 | cross-section, max.: 6, turned, Copper alloy |
| Qty. | 25 ST | |

Crimp contacts HD



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC-C-HD-BM0.14-0.37AG | Version |
| Order No. | 1651570000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400248 | Female, Conductor cross-section, max.: 0.37, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM0.5AG | Version |
| Order No. | 1651580000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400255 | Female, Conductor cross-section, max.: 0.5, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM0.75-1.00AG | Version |
| Order No. | 1601760000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190158354 | Female, Conductor cross-section, max.: 1, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM1.5AG | Version |
| Order No. | 1651600000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400279 | Female, Conductor cross-section, max.: 1.5, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM2.5AG | Version |
| Order No. | 1651610000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400286 | Female, Conductor cross-section, max.: 2.5, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM0.14-0.37AU | Version |
| Order No. | 1651670000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400347 | Female, Conductor cross-section, max.: 0.37, turned, Copper alloy |
| Qty. | 100 ST | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | HDC-C-HD-BM0.5AU | Version |
| Order No. | 1651680000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400354 | Female, Conductor cross-section, max.: 0.5, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM0.75-1.00AU | Version |
| Order No. | 1651690000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400361 | Female, Conductor cross-section, max.: 1, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM1.5AU | Version |
| Order No. | 1651700000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400378 | Female, Conductor cross-section, max.: 1.5, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-BM2.5AU | Version |
| Order No. | 1651710000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, |
| GTIN (EAN) | 4008190400385 | Female, Conductor cross-section, max.: 2.5, turned, Copper alloy |
| Qty. | 100 ST | |

Crimp contacts HX

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.



General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC C HX SM6.0AG | Version |
| Order No. | 1002940000 | Heavy-duty connectors, Crimp contact, MixMate, Male, Conductor |
| GTIN (EAN) | 4032248697229 | cross-section, max.: 6, turned, Copper alloy |
| Qty. | 25 ST | |
| Type | HDC C HX SM4.0AG | Version |
| Order No. | 1002930000 | Heavy-duty connectors, Crimp contact, MixMate, Male, Conductor |
| GTIN (EAN) | 4032248697212 | cross-section, max.: 4, turned, Copper alloy |
| Qty. | 25 ST | |
| Type | HDC C HX SM2.5AG | Version |
| Order No. | 1002920000 | Heavy-duty connectors, Crimp contact, MixMate, Male, Conductor |
| GTIN (EAN) | 4032248697106 | cross-section, max.: 2.5, turned, Copper alloy |
| Qty. | 25 ST | |
| Type | HDC C HX SM10.0AG | Version |
| Order No. | 1526150000 | Heavy-duty connectors, Crimp contact, HQ, Male, Conductor cross- |
| GTIN (EAN) | 4050118332131 | section, max.: 8, turned, Copper alloy |
| Qty. | 25 ST | |
| Type | HDC C HX SM1.5AG | Version |
| Order No. | 1002910000 | Heavy-duty connectors, Crimp contact, MixMate, Male, Conductor |
| GTIN (EAN) | 4032248697090 | cross-section, max.: 1.5, turned, Copper alloy |
| Qty. | 25 ST | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | HDC C HX BM10.0AG | Version |
| Order No. | 1526190000 | Heavy-duty connectors, Crimp contact, HQ, Female, Conductor cross-section, max.: 8, turned, Copper alloy |
| GTIN (EAN) | 4050118332087 | |
| Qty. | 25 ST | |

Crimp contacts HD



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC-C-HD-SM2.5AU | Version |
| Order No. | 1651660000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 2.5, turned, Copper alloy |
| GTIN (EAN) | 4008190400330 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM2.5AG | Version |
| Order No. | 1651560000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 2.5, turned, Copper alloy |
| GTIN (EAN) | 4008190400231 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM1.5AU | Version |
| Order No. | 1651650000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 1.5, turned, Copper alloy |
| GTIN (EAN) | 4008190400323 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM1.5AG | Version |
| Order No. | 1651550000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 1.5, turned, Copper alloy |
| GTIN (EAN) | 4008190400224 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM0.75-1.00AU | Version |
| Order No. | 1651640000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 1, turned, Copper alloy |
| GTIN (EAN) | 4008190400316 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM0.75-1.00AG | Version |
| Order No. | 1601750000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 1, turned, Copper alloy |
| GTIN (EAN) | 4008190134280 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM0.5AU | Version |
| Order No. | 1651630000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 0.5, turned, Copper alloy |
| GTIN (EAN) | 4008190400309 | |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM0.5AG | Version |
| Order No. | 1651530000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, Conductor cross-section, max.: 0.5, turned, Copper alloy |
| GTIN (EAN) | 4008190400200 | |
| Qty. | 100 ST | |

HDC HQ 4/2 FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | HDC-C-HD-SM0.14-0.37AU | Version |
| Order No. | 1651620000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, |
| GTIN (EAN) | 4008190400293 | Conductor cross-section, max.: 0.37, turned, Copper alloy |
| Qty. | 100 ST | |
| Type | HDC-C-HD-SM0.14-0.37AG | Version |
| Order No. | 1651520000 | Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male, |
| GTIN (EAN) | 4008190400194 | Conductor cross-section, max.: 0.37, turned, Copper alloy |
| Qty. | 100 ST | |