

THM WO T 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 8 - 23 mm, 24.5 x 100 mm, white
Order No.	1003380000
Type	THM WO T 24.5/100 WS
GTIN (EAN)	4032248699278
Qty.	1 items

THM WO T 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	24.5 mm	Height (inches)	0.9646 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	838 g		

Temperatures

Operating temperature range	-40...107 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Material colour according to resistance code	9		
Type of printing	neutral		
Version	Self-adhesive		
Width	100 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	107 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	Yes		
Basic material	Tedlar polyvinyl fluoride film®		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	25 x 24.5 mm		
Approval acc. to UL 969	No		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...107 °C		
Number per roll	2000		


Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	120 mm ²
Conductor O.D., max.	23 mm	Conductor O.D., min.	8 mm
Text field width	24.5 mm	Text field height	25 mm
Conductor O.D.	8 - 23 mm	Cross-section for connected wire	120 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings



THM WO T 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		