

## VG PG16-MS54 ZR 7.5-15

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

|                     |  |
|---------------------|--|
| Version             | VG MS ZR (standard brass cable gland, multiseal), Cable glands, PG 16, 6.5 mm, OD min. 7.5 - OD max. 15 mm, Brass, nickel-plated |
| Order No.           | <a href="#">1009620000</a>   |
| Type                | VG PG16-MS54 ZR 7.5-15   |
| GTIN (EAN)          | 4032248714391  |
| Qty.                | 50 items   |
| Delivery status     | Discontinued   |
| Available until     | 2024-08-31T00:00:00+02:00  |
| Alternative product | <a href="#">VG 16-MS68</a>   |

## VG PG16-MS54 ZR 7.5-15

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Length     | 27 mm   | Length (inches) | 1.063 inch |
| Net weight | 25.52 g |                 |            |

### Temperatures

|                       |                |
|-----------------------|----------------|
| Operating temperature | -20 °C...80 °C |
|-----------------------|----------------|

### Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | b5ff1f66-ddba-4739-9fc0-0521ddb52139 |

### General information

|                                      |         |                                      |                      |
|--------------------------------------|---------|--------------------------------------|----------------------|
| Outer cable diameter, max.           | 15 mm   | Outer cable diameter, min.           | 7.5 mm               |
| Operating temperature range, max.    | 80 °C   | Operating temperature range, min.    | -20 °C               |
| Halogen                              | No      | AF size 1                            | 22 mm                |
| AF size 2                            | 24 mm   | Protection degree                    | IP54                 |
| Cable gland                          | PG      | Basic material                       | Brass, nickel-plated |
| Seal insert                          | NBR     | Notch multi-layer sealing diameter 1 | 7.5 mm               |
| Notch multi-layer sealing diameter 2 | 10 mm   | Notch multi-layer sealing diameter 3 | 12.5 mm              |
| Notch multi-layer sealing diameter 4 | 15 mm   | External thread                      | PG 16                |
| Length of thread                     | 6.5 mm  | Torque for cap nut, max.             | 5.00 Nm              |
| Torque for connecting adapter, max.  | 7.50 Nm | Torque for connecting adapter, min.  | 7.50 Nm              |
| Torque for cap nut, min.             | 5.00 Nm |                                      |                      |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000441    | ETIM 9.0    | EC000441    |
| ETIM 10.0   | EC000441    | ECLASS 14.0 | 27-14-08-01 |
| ECLASS 15.0 | 27-14-08-01 |             |             |

## VG PG16-MS54 ZR 7.5-15

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | SKMU PG 16-MS              | Version   |  |
| Order No.  | <a href="#">1694110000</a> | SKMU MS (brass locknut), Locknut, PG 16, 3 mm, Brass, nickel-plated |  |
| GTIN (EAN) | 4008190872274              |   |  |
| Qty.       | 100 ST                     |   |  |

### Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | GWDR PG 16-NP              | Version   |  |
| Order No.  | <a href="#">1719580000</a> | GWDR NP (flat gasket - neoprene), Sealing ring, PG 16, Neoprene |  |
| GTIN (EAN) | 4008190352844              |   |  |
| Qty.       | 100 ST                     |   |  |

### Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | GWDR PG 16-PO              | Version  |  |
| Order No.  | <a href="#">1719480000</a> | GWDR PO (flat gasket - polyethylene), Sealing ring, PG 16, |  |
| GTIN (EAN) | 4008190352745              | Polyethylene   |  |
| Qty.       | 100 ST                     |  |  |