

VG PG21-MS54 ZR 10-19**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS ZR (standard brass cable gland, multiseal), Cable glands, PG 21, 7 mm, OD min. 10 - OD max. 19 mm, Brass, nickel-plated
Order No.	1009630000
Type	VG PG21-MS54 ZR 10-19
GTIN (EAN)	4032248714407
Qty.	25 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00
Alternative product	VG 21-MS68

VG PG21-MS54 ZR 10-19

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	29.5 mm	Length (inches)	1.1614 inch
Net weight	40.41 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

General information

Outer cable diameter, max.	19 mm	Outer cable diameter, min.	10 mm
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Halogen	No	AF size 1	28 mm
AF size 2	30 mm	Protection degree	IP54
Cable gland	PG	Basic material	Brass, nickel-plated
Seal insert	NBR	Notch multi-layer sealing diameter 1	10 mm
Notch multi-layer sealing diameter 2	13 mm	Notch multi-layer sealing diameter 3	16 mm
Notch multi-layer sealing diameter 4	19 mm	External thread	PG 21
Length of thread	7 mm	Torque for cap nut, max.	6.70 Nm
Torque for connecting adapter, max.	10.00 Nm	Torque for connecting adapter, min.	10.00 Nm
Torque for cap nut, min.	6.70 Nm		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

VG PG21-MS54 ZR 10-19
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Accessories
Brass lock nuts, nickel-plated


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG21-MS	Version
Order No.	1719200000	SKMU MS (brass locknut), Locknut, PG 21, 3.5 mm, Brass, nickel-
GTIN (EAN)	4008190352424	plated
Qty.	100 ST	

Neoprene flat gasket - GWDR NP


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG21-NP	Version
Order No.	1719590000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 21, Neoprene
GTIN (EAN)	4008190352851	
Qty.	100 ST	

Polyethylene flat gasket - GWDR PO


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG21-PO	Version
Order No.	1719490000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 21,
GTIN (EAN)	4008190352752	Polyethylene
Qty.	100 ST	