

**SAI-T-5S-PARA**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Version	Y connector, M12, Signal distributor
Order No.	<a href="#">1009370000</a>
Type	SAI-T-5S-PARA
GTIN (EAN)	4032248713622
Qty.	1 items

## SAI-T-5S-PARA

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Net weight 24.64 g

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	4060c755-8d0b-4d43-bdb3-4ffabe9d7497

## Connection data

Group outlet - plug-in connector	M12 socket	Single outlet 1 - plug-in connector	M12 socket
Single outlet 2 - plug-in connector	M12 pin	Tightening torque	M12: 0.8 - 1.2 Nm

## Technical data customisable plug-in connectors

Number of poles	5	Coding	A-coded
Contact surface	Gold-plated	Housing main material	TPU
Contact material	CuZn	Nominal voltage	60 V
Nominal current	4 A	Protection degree	IP65, IP67, IP68, when screwed in
Pollution severity	3	Cable gland	M 12
Shield connection	No	Threaded ring material	Nickel-plated CuZn
Temperature range of housing	-30...+90 °C		

## Standards

Connector standard IEC 61076-2-101

## General data

Number of poles	5	Coding	A-coded
Connection thread	M12	Contact surface	Gold-plated
Housing main material	TPU	Contact material	CuZn
Nominal voltage	60 V	Nominal current	4 A
AF size	13 mm	Protection degree	IP65, IP67, IP68, when screwed in
Pollution severity	3	Cable gland	M 12
Connection 1	M12	Connection 2	Screw
Shield connection	No	Temperature range of housing	-30...+90 °C
Conductor O.D.	-		

## Classifications

ETIM 8.0	EC002925	ETIM 9.0	EC002925
ETIM 10.0	EC002925	ECLASS 14.0	27-44-01-06
ECLASS 15.0	27-44-01-06		

Drawings

Wiring diagram

