

SAIBGS-M-4A-3.5/5.5-M8-IF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited. The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

| | |
|------------|--------------------------------|
| Version | Field attachable connector, M8 |
| Order No. | 1010090000 |
| Type | SAIBGS-M-4A-3.5/5.5-M8-IF |
| GTIN (EAN) | 4032248715299 |
| Qty. | 1 items |

SAIBGS-M-4A-3.5/5.5-M8-IF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

Dimensions and weights

Net weight 30 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

| | | | |
|-------------------------------|---------------------|-------------------------------|----------------------|
| Number of poles | 4 | Coding | none |
| Contact surface | Gold-plated | Type of connection | Screw connection |
| Housing main material | CuZn | Insulation resistance | 108 Ω |
| Cable diameter, max. | 5.5 mm | Cable diameter, min. | 3.5 mm |
| Conductor cross-section, max. | 0.5 mm ² | Conductor cross-section, min. | 0.14 mm ² |
| Nominal voltage | 60 V | Nominal current | 4 A |
| Protection degree | IP67 | Plugging cycles | ≥ 100 |
| Pollution severity | 3 | Gender of contact | Female |
| Shield connection | Yes | Threaded ring material | Diecast zinc |
| Temperature range of housing | -40 ... +85 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002635 | ETIM 9.0 | EC002635 |
| ETIM 10.0 | EC002635 | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 | | |