

## ESG 9/20 L MC NE GE


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |   |
|------------|---|
| Version    | ESG, Device markers x 20 mm, PA 66, Colour: yellow, pluggable |
| Order No.  | <a href="#">1010860000</a>                                    |
| Type       | ESG 9/20 L MC NE GE   |
| GTIN (EAN) | 40322487 1596 1   |
| Qty.       | 200 items   |

## ESG 9/20 L MC NE GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.8 mm | Depth (inches)  | 0.0315 inch |
| Height     | 9 mm   | Height (inches) | 0.3543 inch |
| Width      | 20 mm  | Width (inches)  | 0.7874 inch |
| Net weight | 0.54 g |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.004 kg CO2 eq. |  |

### General data

|   |   |           |  |
|---|---|-----------|--|
| Material colour according to resistance code            | 4   |           |  |
| Version   | pluggable   |           |  |
| Width   | 20 mm   |           |  |
| UL 94 flammability rating                               | V-2   |           |  |
| Operating temperature range, max.                       | 100 °C  |           |  |
| Operating temperature range, min.                       | -40 °C  |           |  |
| Colour  | yellow  |           |  |
| Halogen   | No  |           |  |
| Basic material  | PA 66   |           |  |
| Printed characters                                      | without   |           |  |
| Number of markers per packaging unit compatible printer | Form of supply  | MultiCard |  |
|   | <a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a> |           |  |
| Number of markers per combination                       | 1 MultiCard = Device markers                              |           |  |
| Operating temperature range                             | -40...100 °C  |           |  |
| Application/manufacturer                                | Lumberg   |           |  |

### Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**

