

## DEK 5/6 PLUS MC NE WS


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |  |
|------------|--|
| Version    | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, white |
| Order No.  | <a href="#">1011320000</a>   |
| Type       | DEK 5/6 PLUS MC NE WS  |
| GTIN (EAN) | 4032248717644  |
| Qty.       | 1000 items   |

## DEK 5/6 PLUS MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 6 mm   | Width (inches)  | 0.2362 inch |
| Net weight | 0.09 g |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2 eq. |  |

### General data

|   |   |           |  |
|---|---|-----------|--|
| Material colour according to resistance code            | 9   |           |  |
| Orientation of print                                    | horizontal and vertical                                   |           |  |
| Width   | 6 mm  |           |  |
| UL 94 flammability rating                               | V-2   |           |  |
| Operating temperature range, max.                       | 100 °C  |           |  |
| Operating temperature range, min.                       | -40 °C  |           |  |
| Colour  | white   |           |  |
| Halogen   | No  |           |  |
| Basic material  | Polyamide 66  |           |  |
| Colour of printing                                      | black   |           |  |
| Printed characters                                      | neutral   |           |  |
| Number of markers per packaging unit compatible printer | Form of supply  | MultiCard |  |
|   | <a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a> |           |  |
| Number of markers per combination                       | 1 MultiCard = Terminal marker                             |           |  |
| Operating temperature range                             | -40...100 °C  |           |  |
| Application/manufacturer                                | Weidmueller   |           |  |

### Connector markers

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 6.00 mm |
|-----------------|---------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**



**Drawing**

