

HDC SHIELD LEVER 8 LL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Many demands are made on a connector's shielding. Several tailored solutions are available for meeting these requirements:

- Shield discharge via an EMC cable gland
- The use of shield levers together with shield clips

Shield clips are used to fasten the shielded conductor to the shield lever. The shield clips are available in various sizes for different sized conductors.

General ordering data

Version	Heavy-duty connectors, Accessories, Shield clamp
Order No.	1011380000
Type	HDC SHIELD LEVER 8 LL
GTIN (EAN)	4032248717729
Qty.	1 items

HDC SHIELD LEVER 8 LL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 30 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Version

Installation size	8	Basic material	Sheet steel, galvanized
Suitable for ModuPlug®	No		

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-01-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92
ECLASS 13.0	27-44-02-92	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

HDC SHIELD LEVER 8 LL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Size 8



For the crimp connection, the wire connection level is designed as a crimp contact. The established crimp connection has been used as a standard for decades. Crimp contacts are not delivered with the inserts.

Number of poles: 24

Rated current: 16 A

Rated voltage: 500 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

General ordering data

Type	HDC HE 24 FC	Version
Order No.	1211600000	HDC insert, Female, 500 V, 16 A, Number of poles: 24, Crimp
GTIN (EAN)	4008190033200	connection, Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 MC	Version
Order No.	1211500000	HDC insert, Male, 500 V, 16 A, Number of poles: 24, Crimp
GTIN (EAN)	4008190042097	connection, Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 MP	Version
Order No.	1873590000	HDC insert, Male, 500 V, 16 A, Number of poles: 24, PUSH IN,
GTIN (EAN)	4032248458202	Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 FP	Version
Order No.	1873580000	HDC insert, Female, 500 V, 16 A, Number of poles: 24, PUSH IN,
GTIN (EAN)	4032248458196	Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 N FQT BL	Version
Order No.	2535140000	HDC insert, Female, 500 V, 16 A, Number of poles: 24, SNAP IN,
GTIN (EAN)	4050118578256	Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 N MQT BL	Version
Order No.	2535100000	HDC insert, Male, 500 V, 16 A, Number of poles: 24, SNAP IN,
GTIN (EAN)	4050118578249	Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 FS	Version
Order No.	1211300000	HDC insert, Female, 500 V, 16 A, Number of poles: 24, Screw
GTIN (EAN)	4008190067298	connection, Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 MS	Version
Order No.	1211100000	HDC insert, Male, 500 V, 16 A, Number of poles: 24, Screw
GTIN (EAN)	4008190181703	connection, Installation size: 8
Qty.	1 ST	
Type	HDC HE 24 MS W/O SCREW	Version
Order No.	1713600000	HDC insert, Male, 500 V, 16 A, Number of poles: 24, Screw
GTIN (EAN)	4008190331061	connection, Installation size: 8
Qty.	5 ST	
Type	HDC HE 24 MT	Version
Order No.	1745850000	HDC insert, Male, 500 V, 16 A, Number of poles: 24, Tension-clamp
GTIN (EAN)	4008190985578	connection, Installation size: 8
Qty.	1 ST	

HDC SHIELD LEVER 8 LL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	HDC HE 24 FT	Version
Order No.	1745790000	HDC insert, Female, 500 V, 16 A, Number of poles: 24, Tension-clamp
GTIN (EAN)	4008190985516	connection, Installation size: 8
Qty.	1 ST	